

[See all 19 Products in Family](#)

**TECHSPEC® 12.7mm Dia. x 200mm ROC, Uncoated, Convex Laser Mirror**



Stock #27-603 **NEW** 5 In Stock

⊖ 1 ⊕ MRP ₹12,107

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹12,107 each
Qty 6-25	₹11,501 each
Qty 26+	₹11,199 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

ConvexMirror **Type:**

**Physical & Mechanical Properties**

5.90 **Center Thickness CT (mm):**

5.9 **Clear Aperture CA (mm):**

12.70 +0.00/-0.12	<b>Diameter (mm):</b>
6.00 ±0.2	<b>Edge Thickness ET (mm):</b>
90	<b>Clear Aperture (%):</b>
Commercial Polish	<b>Back Surface:</b>

## Optical Properties

<b>Fused Silica</b> (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>
200.00	<b>Radius R<sub>1</sub> (mm):</b>
20-10	<b>Surface Quality:</b>
Uncoated	<b>Coating:</b>
6.00	<b>Effective Focal Length EFL (mm):</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
Vietnam	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- High Precision Fused Silica Mirror Substrates
- Large Selection of Diameters and Focal Lengths
- Custom Coating Options Available

TECHSPEC® Uncoated Convex Laser Mirrors offer high precision 20-10 surface quality ideal for laser beam focusing applications. Featuring fused silica substrates, these convex mirrors are resistant to thermal shock and are available in focal lengths from 25mm to 500mm. TECHSPEC Uncoated Convex Laser Mirrors are ideal for applications in environments with temperature fluctuations. Custom coating options including protected metal coatings and dielectric mirror coatings are available.