

TECHSPEC[®] 12.7mm Thick Inner Pair Optic Mounts



12.7mm Thick Inner Pair Optic Mounts

Stock #11-053 17 In Stock

-

1

+

₹4,878

ADD TO CART

Volume Pricing	
Qty 1-4	₹4,878 each
Qty 5+	₹4,687 each
Need More?	Request Quote

Product Downloads

General

Fixed	Type:
Optic Mount (Fixed)	Function:

Physical & Mechanical Properties

Matte Black Anodized Aluminum (6061-T6)	Construction:
	Total Length (mm):

28	
	Clear Aperture CA (mm):
11.2	
	Max. Thickness of Compatible Optics (mm):
9.0	
	Min. Thickness of Compatible Optics (mm):
1.0	
	Edge Thickness of Compatible Optics (mm):
9.0	

Threading & Mounting	
	Diameter of Compatible Optics (mm):
12.7	
	Thread Type:
M29 x0.75	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 250:
Compliant	
	Country of Origin:
China	
	Imported By:
Edmund Optics India Private Limited	

Product Details

- Facilitate Imaging System Construction
 - Combine Lenses to Create Specific Magnifications for a Wide Wavelength Range
 - Use Multi-Element Tubes and Accessories to Create Complete Imaging Systems
 - Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.
- TECHSPEC® Multi-Element Inner Pair Optic Mounts enable the combination of two optics of the same diameter in a single mount with a constant distance between them. Combining different lenses of varying focal lengths allows for the creation of relay lens assemblies. Choose from our Optical Lenses the correct wavelength specification for your application to create your ideal imaging system. The mounts support optical diameters from 12mm to 25mm, and edge thicknesses from 4mm to 16.5mm. With M29 x0.75 threads on the outer diameter, these mounts can easily be positioned along the optical axis of our TECHSPEC® Multi-Element Outer Tubes. TECHSPEC® Multi-Element Inner Pair Optic Mounts come with two Delrin rings to ensure secure clamping force between the retainer rings and optics without damaging the optics.
- Note:** Our specially designed ME Spanner Wrench ([#13-567](#)) is highly recommended to move Inner Pair Optic Mounts back and forth smoothly utilizing a combined metric and English graduated scale. The hollow design enables transmission of output beam while adjusting lens position. Non-scaled ME Spanner Wrench ([#11-046](#)) is also available.