

[See all 5 Products in Family](#)

## 12mm, 0.365mm Focal Length, Fast Axis Collimator



Fast Axis Collimators

Stock **#87-350** **8 In Stock**

⊖ 1 ⊕ ₹15,414

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹15,414 each
Qty 11-49	₹13,857 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Beam Shaping Lens **Type:**

### Physical & Mechanical Properties

11.0 x 0.55 **Clear Aperture CA (mm):**

1.50 **Height (mm):**

**Height Tolerance (mm):**

±0.05

Length (mm):

12.00

Length Tolerance (mm):

±0.05

Width (mm):

0.50

Width Tolerance (mm):

±0.01

## Optical Properties

Effective Focal Length EFL (mm):

0.36

Substrate:

[S-TiH53](#)

f#:

0.77

Numerical Aperture NA:

0.65

Coating:

BBAR (790-990nm)

Wavelength Range (nm):

790 - 990

Back Focal Length BFL (mm):

0.095

Coating Specification:

R<sub>avg</sub> <1.0% @ 790 - 990nm

Surface Accuracy:

λ/4

Transmission (%):

>99

## Electrical

Power Distribution (%):

within ±1.75: >85

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

Reach 197:

[Compliant](#)

Certificate of Conformance:

[View](#)

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited

## Product Details

- Aspheric Cylindrical Lens Designs for Fast Axis Collimation
- Standard AR Coating for 790 – 990nm
- Ideal for Laser Diode Collimation
- [Slow Axis Collimators](#) Also Available

Fast Axis Collimators are compact, high performance aspheric cylindrical lenses designed for beam shaping or laser diode collimation applications. The aspheric cylindrical designs and high numerical apertures allow for uniform collimation of the entire output of a laser diode while maintaining high beam quality. Fast Axis Collimators feature greater than 99% transmission across the designated spectral range, and are available in a variety of focal lengths.

**LASER OPTICS** MADE BY EDMUND OPTICS®

[LEARN MORE](#)