

[See all 10 Products in Family](#)

## 12mm Dia. x 12mm FL, Small Diameter Plastic Aspheric Lens



Stock #15-275 **20+ In Stock**

- 1 + MRP ₹4,137

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹4,137 each
Qty 11-49	₹3,430 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Aspheric Lens **Type:**

#### Physical & Mechanical Properties

12.00 ±0.20 **Diameter (mm):**

**Clear Aperture CA (mm):**

12.00

Edge Thickness ET (mm):

3.42

Center Thickness CT (mm):

7.00 ±0.20

## Optical Properties

Effective Focal Length EFL (mm):

12.00

Numerical Aperture NA:

0.50

Back Focal Length BFL (mm):

6.99

Substrate:

Acrylic V825

Focal Length Tolerance (%):

±1.5

Aspheric Design Wavelength (nm):

550

Coating:

Uncoated

Surface Quality:

60-40

f/#:

1.00

Design Wavelength DWL (nm):

550

Index of Refraction (n<sub>d</sub>):

1.491

## Regulatory Compliance

RoHS 2015:

Compliant

Reach 224:

Compliant

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Small Diameter Eases OEM Integration
- High Numerical Apertures
- Ideal for Medical and Diagnostic Instrumentation

Small Diameter Plastic Aspheric Lenses are designed with OEM integration in mind. The small diameters, lightweight materials, and high numerical apertures make these lenses ideal for medical devices, diagnostic instrumentation, or wearable applications. Full prescription data is available to assist in design integration.

**Note:** For custom coating requirements, please [contact us](#).

## Compatible Mounts