

[See all 10 Products in Family](#)

12mm Dia. x 12mm FL, Small Diameter Plastic Aspheric Lens



Stock #15-275 **20+ In Stock**

⊖ 1 ⊕ ₹2,919

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | ₹2,919 each |
| Qty 11-49 | ₹2,433 each |
| Need More? | Request Quote |

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

12.00 ±0.20 **Diameter (mm):**

12.00 **Clear Aperture CA (mm):**

| | |
|-------------------------------------|-------------------------------------|
| 3.42 | Edge Thickness ET (mm): |
| 7.00 ±0.20 | Center Thickness CT (mm): |
| Optical Properties | |
| 12.00 | Effective Focal Length EFL (mm): |
| 0.50 | Numerical Aperture NA: |
| 6.99 | Back Focal Length BFL (mm): |
| Acrylic V825 | Substrate: <input type="checkbox"/> |
| ±1.5 | Focal Length Tolerance (%): |
| 550 | Aspheric Design Wavelength (nm): |
| Uncoated | Coating: |
| 60-40 | Surface Quality: |
| 1.00 | f#: |
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| Compliant | Reach 224: |
| View | Certificate of Conformance: |
| United States | Country of Origin: |
| Edmund Optics India Private Limited | Imported By: |

Product Details

- Small Diameter Eases OEM Integration
- High Numerical Apertures
- Ideal for Medical and Diagnostic Instrumentation

Small Diameter Plastic Aspheric Lenses are designed with OEM integration in mind. The small diameters, lightweight materials, and high numerical apertures make these lenses ideal for medical devices, diagnostic instrumentation, or wearable applications. Full prescription data is available to assist in design integration.

Note: For custom coating requirements, please [contact us](#).

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts