

## 12mm Dia. x 19mm FL, Aspheric Condenser Lens, VIS-EXT



Stock #72-482 **10 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹5,499

● Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹5,499 each                   |
| Qty 11-49      | ₹5,045 each                   |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

#### General

Condenser Lens **Type:**

#### Physical & Mechanical Properties

12.00 +0.0/-0.2 **Diameter (mm):**

≤30 **Centering (arcmin):**

|                                     |  |
|-------------------------------------|--|
| 10.80                               | <b>Clear Aperture CA (mm):</b>             |
| 3.12                                | <b>Edge Thickness ET (mm):</b>             |
| 5.00 ±0.30                          | <b>Center Thickness CT (mm):</b>           |
| Protective as needed                | <b>Bevel:</b>                              |
| 12.00                               | <b>Diameter of Asphere (mm):</b>           |
| Plano                               | <b>Shape of Back Surface:</b>              |
| <b>Optical Properties</b>           |  |
| 19.00                               | <b>Effective Focal Length EFL (mm):</b>    |
| 0.32                                | <b>Numerical Aperture NA:</b>              |
| 15.70                               | <b>Back Focal Length BFL (mm):</b>         |
| H-K51                               | <b>Substrate:</b> <input type="checkbox"/> |
| ±5                                  | <b>Focal Length Tolerance (%):</b>         |
| MS-EXT (350-700nm)                  | <b>Coating:</b>                            |
| R <sub>avg</sub> <0.5% @350 - 700nm | <b>Coating Specification:</b>              |
| 80-50 (typical)                     | <b>Surface Quality:</b>                    |
| 1.58                                | <b>f#:</b>                                 |
| ∞                                   | <b>Radius R<sub>2</sub> (mm):</b>          |
| 350 - 700                           | <b>Wavelength Range (nm):</b>              |
| Infinite                            | <b>Conjugate Distance:</b>                 |

|  |                                    |
|--|------------------------------------|
| <b>Regulatory Compliance</b>   |                                    |
| <a href="#">View</a>   | <b>Certificate of Conformance:</b> |
| China  | <b>Country of Origin:</b>          |
| <b>Imported By:</b><br>Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 |                                    |

## Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

## Technical Information



