

[See all 88 Products in Family](#)

12mm Dia. x 7.5mm FL, VIS-EXT Coated Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#71-486** **6 In Stock**

☐ [Other Coating Options](#)

-

1

+

MRP ₹5,236

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹5,236 each
Qty 11-49	₹4,731 each
Need More?	Request Quote

Product Downloads

General	
Condenser Lens	Type:
Click here for more information on the ISO 10110 surface quality specification.	Note:
Physical & Mechanical Properties	
	Diameter (mm):

12.00 +0.0/-0.3	
Centering (arcmin):	≤30
Clear Aperture CA (mm):	9.50
Edge Thickness ET (mm):	1.85
Center Thickness CT (mm):	5.50 ±0.20
Bevel:	Protective as needed
Diameter of Asphere (mm):	12.0
Shape of Back Surface:	Convex

Optical Properties	
Effective Focal Length EFL (mm):	7.50 @ 587.6nm
Numerical Aperture NA:	0.80
Back Focal Length BFL (mm):	4.60
Substrate: □	Liba2000+
Focal Length Tolerance (%):	±5
Coating:	VIS-EXT (350-700nm)
Coating Specification:	R _{avg} ≤0.4% @ 425 - 675nm
Surface Quality:	5/3 x0.4; E 0.2
f##:	0.63
Radius R ₂ (mm):	12.7
Wavelength Range (nm):	350 - 700
Conjugate Distance:	Infinite


Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 242:	Compliant
Country of Origin:	Germany
Imported By:	Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000

Product Details

- Hardened for Improved Durability
- High Numerical Apertures
- Ideal for Illumination Applications

Molded Aspheric Condenser Lenses are pressed, hardened, and annealed to meet precise optical and mechanical specifications. The hardening process improves the durability of the lenses, making them less susceptible to thermal shock and scratching than traditionally polished lenses. These Molded Aspheric Condenser Lenses are ground and polished on the second surface, enhancing the overall precision of the lenses. Molded Aspheric Condenser lenses are ideal for a wide range of illumination and detection applications, including biotech instruments such as DNAsequencers and polymerase chain reaction (PCR) testing platforms.

Technical Information



;