

[See all 24 Products in Family](#)

Ti:Sapphire Flat Top Beam Shaper 12mm | πShaper 12_12_TiS_HP

See More by [AdlOptica](#)



Stock #14-279 **1 In Stock**

- 1 + MRP ₹10,66,703

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹10,66,703 each
Qty 5-10	₹9,60,606 each
Qty 11+	₹9,07,080 each
Need More?	Request Quote

Product Downloads

General

πShaper 12_12_TiS_HP **Model Number:**

Beam Shaper **Type:**

Flat Top **Style:**

Physical & Mechanical Properties

358.00 **Length (mm):**

<530 **Weight (g):**

42.00 **Diameter (mm):**

Optical Properties

12.0 - 12.1 **Entrance Beam Diameter, 1/e² (mm):**

800 **Design Wavelength DWL (nm):**

700 - 900 **Wavelength Range (nm):**

3000 mJ/cm² @ 5ns (typical) **Damage Threshold, By Design:**

12.0 **Output Diameter, FWHM (mm):**

3000 mJ/cm² @ 5ns (typical) **Damage Threshold, Pulsed:**

Threading & Mounting

M27 x 1 **Mounting Threads:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

Germany **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000 **Imported By:**

Product Details

- Convert Gaussian Beam Profile to Flat Top Profile
- Near 100% Efficiency
- No Internal Focusing Enables High Power Laser Input
- [AdlOptica Focal- \$\pi\$ Shaper Q Flat Top Beam Shapers](#) Also Available

AdlOptica π Shaper (piShaper) Flat Top Beam Shapers are refractive field mapping optical systems that convert collimated Gaussian input beams into collimated flat top beams with a uniform intensity distribution and flat phase front. Due to the field mapping optical design, the even intensity distribution of the converted beam is stable over great distances making it ideally suitable for holography, microscopy, system integration and ultrafast applications. With no internal focusing, they are also the perfect solution in applications such as material micromachining, welding, and engraving that require high power lasers. These AdlOptica π Shaper Flat Top Beam Shapers are offered in common YAG, fiber laser, and CO₂ laser sources, operating over a defined wavelength range for laser tuning. Achromatic versions are designed to be used with multiple laser sources.

Note: Focusing a flat-top beam after a π Shaper results in loss of the flat top profile. [AdlOptica Focal- \$\pi\$ Shaper Q Flat Top Beam Shapers](#) are available for applications that require a focused flat top spot.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

Technical Information

Example of beam shaping for TEM₀₀ Laser

