

[See all 13 Products in Family](#)

130mm x 100mm Travel, Linear Motor XY Microscope Stage, Integrated Controller, Linear Encoder

See More by [Zaber™](#)



130mm x 100mm Travel, Linear Motor XY Microscope Stage, Integrated Controller, Linear Encoder

Stock **#70-660** **1 In Stock**

⊖ 1 ⊕ MRP ₹11,20,410

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹11,20,410 each
Need More?	Request Quote

Product Downloads

General

Metric **Type:**

Yes **Encoder:**

Zaber Technologies Inc. **Manufacturer:**

Moving Magnet Track Linear Motor **Type of Motor:**

Linear Analog Encoder **Encoder Type:**

Physical & Mechanical Properties

Linear (X-Y) **Type of Movement:**

Crossed Roller Bearing **Guide System:**

280.5 x 381.9 **Stage Size (mm):**

130 in X 100 in Y **Travel (mm):**

5 (Unidirectional)	Accuracy (µm):
0	Backlash (µm):
40.6	Height (mm):
5.08, Centered Load	Load Capacity (kg):
<0.5	Repeatability (µm):
0.00000065 to 750	Speed (mm/s):
35	Thrust (N):
4.9	Weight (kg):
1nm	Encoder Resolution:

Optical Properties

0.001	Resolution (µm):
-------	-------------------------

Electrical

2300	Maximum Operating Current (mA):
------	--

Hardware & Interface Connectivity

Direct Drive Linear Motor	Type of Drive:
Power Supply Required and Sold Separately. USA: #15-294 Europe: #15-294 Japan: #23-662 Korea: #33-773 China: #15-294	Power Supply:

RS-232	Computer Interface:
--------	----------------------------

Environmental & Durability Factors

0 to 50	Operating Temperature (°C):
---------	------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	Reach 247:
---------------------------	-------------------

Canada	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Ultra-Quiet Linear Motors
- 130 x 100mm or 250 x 100mm Travel Options Available
- 1nm Resolution Linear Encoders provide Excellent Accuracy, Repeatability, and Speed
- Compatible with [µManager](#) Open-Source Microscopy Software

Zaber™ Linear Motor XY Microscope Motorized Stages feature ultra-quiet non-contact linear motors and optical linear encoders that are ideal for microscopy applications where speed, accuracy and reliability are of utmost importance. These stages have compact controllers built directly into the stage that allow both axes to be powered and independently controlled through a single cable. Adapter plates are available for mounting the stage to breadboards ([#70-662](#)), and for direct integration into Nikon ([#70-663](#)), and Olympus ([#70-664](#)) microscope systems. Zaber™ Linear Motor XY Microscope Motorized Stages are designed with 1nm Resolution Linear Encoders which provides 5µm Travel Accuracy, <0.5µm Repeatability, 50nm Incremental Movement, and speeds up to 750mm/s. These stages are fully supported by [µManager](#) Open-Source Microscopy Software as well as [Zaber Launcher](#) and [Zaber's Motion Library](#).

Note: A [48 VDC universal power supply](#), [data cables](#) for daisy chaining, and computer interface cables ([USB](#) or [RS-232](#)) are sold separately as accessories.