

TECHSPEC® 150mm Dia., 0.50 Numerical Aperture NIR Coated, Aspheric Lens



Stock **#22-721** **3 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ ₹1,77,109

ADD TO CART

Volume Pricing	
Qty 1-5	₹1,77,109 each
Qty 6+	₹1,41,687 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

150.00 +0.0/-0.1 **Diameter (mm):**

≤5 **Centering (arcmin):**

Clear Aperture CA (mm):

128

Edge Thickness ET (mm):

7.51

Center Thickness CT (mm):

48.30 ±0.1

Bevel:

Protective as needed

Shape of Back Surface:

Plano

Optical Properties

Effective Focal Length EFL (mm):

150.00 @ 587.6nm

Numerical Aperture NA:

0.50

Back Focal Length BFL (mm):

118.16

Substrate:

N-BK7

Asphere Figure Error, RMS @ 632.8nm:

1.2λ

Coating:

BBAR (600-1050nm)

Coating Specification:

R_{avg} ≤ 1.5% @ 600 - 1050nm

Surface Quality:

60-40

f#:

1.00

Wavelength Range (nm):

350 - 2200

Conjugate Distance:

Infinite

Power (diopters):

6.67

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

View

Reach 250:

Compliant

Country of Origin:

Singapore

Imported By:

Edmund Optics India Private Limited

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Diameters from 10 to 200mm
- Focal Lengths from 7.5 to 300mm
- Broadband AR Coatings Available

TECHSPEC® Aspheric Lenses are designed to focus light while eliminating spherical aberration from divergent light sources in applications including focusing the output of a laser diode. [Aspheric lenses can increase the numerical aperture of a lens while minimizing system aberrations](#). Aspheric lenses may also reduce the number of elements needed in a multi-element system. Aspheric lenses can reduce overall system weight while providing advantages such as increasing throughput or simplifying assembly.

TECHSPEC Aspheric Lenses feature low f#s for optimum light gathering performance. Prescription data is available to easily integrate these aspheric lenses into an optical system. These lenses have also been computer optimized to eliminate spherical aberration while minimizing higher order aberrations. MS coating option provides less than 1.5% reflection from 425 – 675nm. NIR coating option provides less than 1.5% reflection from 600 – 1050nm. Contact our sales department for volume pricing or for help specifying a custom aspheric lens.

Technical Information

