

**TECHSPEC®**

## 15mm Dia., 0.83 Numerical Aperture, 900-1700nm Coated, Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#22-759** **10 In Stock**

[Other Coating Options](#)

MRP ₹44,291

Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹44,291 each                  |
| Qty 6-10       | ₹39,852 each                  |
| Qty 11-25      | ₹36,320 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

### General

Aspheric Lens **Type:**

### Physical & Mechanical Properties

15.00 +0.00/-0.025 **Diameter (mm):**

|                      |                                  |
|----------------------|----------------------------------|
| <3                   | <b>Centering (arcmin):</b>       |
| 13.50                | <b>Clear Aperture CA (mm):</b>   |
| 5.28                 | <b>Edge Thickness ET (mm):</b>   |
| 9.70 ±0.10           | <b>Center Thickness CT (mm):</b> |
| Protective as needed | <b>Bevel:</b>                    |
| Plano                | <b>Shape of Back Surface:</b>    |

## Optical Properties

|                                                                                                                                       |                                             |
|---------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------|
| 9.00 @ 587.6nm                                                                                                                        | <b>Effective Focal Length EFL (mm):</b>     |
| 0.83                                                                                                                                  | <b>Numerical Aperture NA:</b>               |
| 3.63                                                                                                                                  | <b>Back Focal Length BFL (mm):</b>          |
| <a href="#">N-SF6</a>                                                                                                                 | <b>Substrate:</b> <input type="checkbox"/>  |
| 0.4λ                                                                                                                                  | <b>Asphere Figure Error, RMS @ 632.8nm:</b> |
| SWIR+ (900-1700nm)                                                                                                                    | <b>Coating:</b>                             |
| <b>Coating Specification:</b><br>R <sub>avg</sub> <0.5% @ 900 - 1700nm @ ±30° AOI<br>R <sub>abs</sub> <1.5% @ 900 - 1700nm @ ±30° AOI |                                             |
| 40-20                                                                                                                                 | <b>Surface Quality:</b>                     |
| 1.00                                                                                                                                  | <b>f#:</b>                                  |
| 900 - 1700                                                                                                                            | <b>Wavelength Range (nm):</b>               |
| Infinite                                                                                                                              | <b>Conjugate Distance:</b>                  |
| 111.11                                                                                                                                | <b>Power (diopters):</b>                    |

## Regulatory Compliance

|                                                                                                                                                                                                                                |                                    |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------|
| <a href="#">Compliant</a>                                                                                                                                                                                                      | <b>RoHS 2015:</b>                  |
| <a href="#">View</a>                                                                                                                                                                                                           | <b>Certificate of Conformance:</b> |
| <a href="#">Compliant</a>                                                                                                                                                                                                      | <b>Reach 250:</b>                  |
| Singapore                                                                                                                                                                                                                      | <b>Country of Origin:</b>          |
| <b>Imported By:</b><br>Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 |                                    |

## Product Details

- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.