

[See all 96 Products in Family](#)

## 15µm Aperture Diameter, Mounted, Precision Pinhole



15µm Aperture Diameter, Mounted, Precision Pinhole, #56-278

Stock **#56-278** **6 In Stock**

- 1 + MRP ₹9,635

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-5	₹9,635 each
Qty 6-10	₹8,526 each
Qty 11+	₹7,889 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Mounted **Type:**

### Physical & Mechanical Properties

25 +0.4/-0.000 **Outer Diameter (mm):**

**Construction:**

Stainless Steel

Fixed Aperture Diameter ( $\mu\text{m}$ ):

15

Thickness (mm):

0.01 Nominal

Aperture Tolerance ( $\mu\text{m}$ ):

$\pm 5$

Aperture Centration ( $\mu\text{m}$ ):

$\pm 125$

## Threading & Mounting

Mount Thickness (mm):

1.25  $\pm 0.05$

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Available in Aperture Mounts for a Secure Mechanical Support
- Pinhole Sized Ranging from 1 to 1,000 Microns
- [High Power Apertures](#) Available

### Unmounted Precision Pinholes

Precision Pinholes are high quality apertures centered to  $\pm 0.002''$  (50 microns). They are constructed of stainless steel and are 3/8" (9.5mm) in diameter. Smaller diameter pinholes will reduce energy throughput, while larger diameter pinholes will pass more spatial noise. Precision pinholes have sizes ranging from 1 to 1,000 microns. Typical applications include leak detection, aerosol studies, holography, fiber optics guides, spatial filtering, research, and more.

Use the [Precision Pinhole Mount](#) to integrate unmounted pinholes into a variety of mechanical components easily.

### Mounted Precision Pinholes

Precision Pinholes are available in aperture mounts for secure mechanical support. The mounts also fit into various optical assemblies. Each 9.5mm diameter pinhole is sealed within a 25mm diameter black-anodized aluminum mount. The mount is clearly labeled with a pinhole aperture diameter for easy identification.

**Note:** Aperture Centering to Mount  $\pm 125$  microns.

Edmund Optics offers a wide selection of precision pinholes for leak detection, aerosol studies, holography, fiber optic guides, spatial filtering, research, and more. These pinholes are available in a range of diameters and are ideal for controlling light propagation. Each pinhole is manufactured using high-accuracy techniques, providing consistent circular aperture geometry and high edge quality. Available in both mounted and unmounted formats, these pinholes support a variety of optical setups, from experimental labs to industrial environments.

## Technical Information

