

[See all 97 Products in Family](#)

**TECHSPEC® 16mm FL f/2.5 Blue Series IR-Cut M12 Lens**



Stock #24-462 **20+ In Stock**

- 1 + MRP ₹9,027

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-49	₹9,027 each
Qty 50+	₹7,143 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Blue Series **Product Family:**  
M12 Imaging Lens **Type:**  
Yes **IR Cut Filter:**

IR-Cut Filter      **Special Type of Lens:**

## Physical & Mechanical Properties

Fixed      **Iris Option:**  
  
22.50      **Length (mm):**

16      **Maximum Diameter (mm):**

16      **Outer Diameter (mm):**

## Optical Properties

**Horizontal Field of View @ Max Sensor Format:**  
25.3°

**Field of View at Max Sensor Format:**  
Horizontal: 64.9mm - 25.3°  
Vertical: 48.7mm - 19.1°  
Diagonal: 81.2mm - 31.4°

**Horizontal Field of View, 1.2" Sensor:**  
58.0mm - 22.5°

**Horizontal Field of View, 1/1.8" Sensor:**  
64.9mm - 25.3°

**Horizontal Field of View, 1/2.5" Sensor:**  
52.5mm - 20.5°

**Horizontal Field of View, 1/3" Sensor:**  
43.5mm - 17.0°

**Horizontal Field of View, 1/4" Sensor:**  
32.6mm - 12.8°

9.00      **Maximum Image Circle (mm):**

0.026544      **Numerical Aperture NA, Object Side:**

6 (6)      **Number of Elements (Groups):**

400 - 700      **Wavelength Range (nm):**

16.00      **Focal Length FL (mm):**

150 - ∞      **Working Distance (mm):**

f/2.5      **Aperture (f/#):**

-0.039@Full Field      **Distortion (%):**

10.79 - 10.05      **Back Focal Length BFL (mm):**

M4 MgF<sub>2</sub> @ 588nm      **Coating Specification:**

7.5143      **Entrance Pupil Position (mm):**

7.21      **Object Space Principal Plane (mm):**

-7.04      **Image Space Principal Plane (mm):**

-0.039      **Maximum Distortion (%):**

-6.7445      **Exit Pupil Position (mm):**

VIS (IR-Cut Filter)      **Lens Wavelength Range:**

## Sensor

1/1.8"      **Maximum Sensor Format:**

1.40      **Pixel Size (µm):**

## Threading & Mounting

N/A      **Filter Thread:**

S-Mount (M12 x0.5)      **Mount:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**

**China** **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Up to 1/2", S-Mount Lens
- Up to 5 MegaPixels, 1.4µm Pixel Size Sensors
- High Resolution Board Camera Lens Optimized for Close WD
- 2mm to 35mm Focal Length
- **Ruggedized Designs** Also Available

TECHSPEC® Blue Series M12 Lenses feature high resolution performance, along with the same great versatility of our **TECHSPEC® Green Series M12 Lenses**. Each lens consists of several precision glass elements mounted in a compact, aluminum housing. These lenses can connect to C-Mount cameras using the M12 x 0.5 Adapter for C-Mount Cameras (**#53-675**) or the M12 x 0.5 C-Mount Adapter with Rubber O-Ring (**#59-241**) for vibration-sensitive environments. TECHSPEC® Blue Series M12 Lenses are ideal for automotive, industrial, and medical imaging application. Prescription data is available by submitting a **Request for Prescription Form**.

**Note:** Compatible **TECHSPEC® M12 Imaging Lens Accessories** available.

Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- **Blue Series M12 Lenses:** High resolution finite conjugate designs optimized for machine vision working distances.
- **Rugged Blue Series M12 Lenses:** **Stabilized ruggedization** versions of our Blue Series M12 Lenses, utilizing the same optics.
- **Green Series M12 Lenses:** Finite conjugate designs optimized for machine vision working distances.
- **Red Series M12 Lenses:** Infinite conjugate designs optimized for high resolution performance out to infinity.
- **HEO Series M12 Lenses:** Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- **Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.

## Technical Information

Focal Length	A	B	C*	D
2.0mm	18.0mm	21.7mm	2.26mm	4.75mm
3.0mm	14.0mm	17.1mm	4.8 - 4.7mm	5.8mm
4.0mm	14.0mm	19.7mm	6.1 - 6.0mm	4.4mm
5.0mm	14.0mm	14.6mm	4.0 - 3.9mm	3.7mm
6.0mm	14.0mm	14.1mm	6.9 - 6.8mm	4.5mm
8.0mm	14.0mm	12.3mm	8.8 - 8.6mm	3.7mm
10.0mm	14.0mm	17.0mm	6.6 - 6.3mm	3.7mm
12.5mm	15.0mm	22.9mm	10.1 - 9.7mm	4.8mm
17.5mm	14.0mm	20.7mm	5.8 - 4.9mm	7.6mm
25.0mm	18.0mm	30.0mm	8.5 - 6.5mm	11.5mm
35.0mm	18.0mm	29.5mm	18.72 - 14.0mm	14.5mm



\*Specified for Optimized Working Distance of 150 - 250mm.