

## 16mm FL SWIR Series Fixed Focal Length Lens



Stock **#83-817** **2 In Stock**

⊖ 1 ⊕ MRP ₹2,42,819

📌 Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹2,42,819 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Product Family:**  
1" SWIR Series Fixed Focal Length Lenses

**Type:**  
Fixed Focal Length Lens

### Physical & Mechanical Properties

**Iris Option:**  
Variable

**Length (mm):**  
52.90

42.0	<b>Maximum Diameter (mm):</b>
42	<b>Outer Diameter (mm):</b>
150	<b>Weight (g):</b>
<b>Optical Properties</b>	
235	<b>Field of View @ Min Working Distance (mm):</b>
44.3°	<b>Horizontal Field of View, 1" Sensor:</b>
16.00	<b>Maximum Image Circle (mm):</b>
16.00	<b>Focal Length FL (mm):</b>
300 - ∞	<b>Working Distance (mm):</b>
f/1.4 - f/16	<b>Aperture (f/#):</b>
<-1.0	<b>Distortion (%):</b>
-1	<b>Maximum Distortion (%):</b>
SWIR	<b>Lens Wavelength Range:</b>
<b>Sensor</b>	
1"	<b>Maximum Sensor Format:</b>
4.50	<b>Pixel Size (µm):</b>
<b>Threading &amp; Mounting</b>	
M35.5 x 0.50	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>
<b>Regulatory Compliance</b>	
<a href="#">Exempt</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Contains SVHC(s)</a>	<b>REACH 241:</b>
Japan	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- 1", C-Mount Lens
- Spectral Range of 800 - 2000nm for InGaAs SWIR Sensors
- 8mm to 50mm Focal Lengths

Short Wave Fixed Focal Length Lenses are the best choice for use with SWIR cameras. The SWIR spectrum is an ideal choice for a variety of applications, including solar cell inspection, security, and biomedical imaging. When utilized in conjunction with a SWIR camera, these lenses will permit imaging through silicon, imaging outdoors without additional illumination, detecting bruising on fruit, and a host of additional infrared applications.

## Technical Information

### SWIR Fixed Focal Length Lenses

