

[See all 9 Products in Family](#)

## 16mm Focal Length Lens, 1" Sensor Format



16mm Focal Length Lens, 1" Sensor Format, #63-245

Stock **#63-245** **5 In Stock**

[Similar Products](#)

⊖ 1 ⊕ MRP ₹94,215

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹94,215 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Product Family:**  
1" Format Fixed Focal Length Lenses

**Type:**  
Fixed Focal Length Lens

### Physical & Mechanical Properties

**Iris Option:**  
Variable

**Length (mm):**

52.90	
42.0	<b>Maximum Diameter (mm):</b>
42	<b>Outer Diameter (mm):</b>
140	<b>Weight (g):</b>

## Optical Properties

44.3°	<b>Horizontal Field of View, 1" Sensor:</b>
16.00	<b>Maximum Image Circle (mm):</b>
<1.0	<b>TV Distortion (%):</b>
16.00	<b>Focal Length FL (mm):</b>
300 - ∞	<b>Working Distance (mm):</b>
f/1.4 - f/16	<b>Aperture (f/#):</b>
< -1.0%	<b>Maximum Distortion (%):</b>
VIS	<b>Lens Wavelength Range:</b>

## Sensor

1"	<b>Maximum Sensor Format:</b>
5.00	<b>Pixel Size (µm):</b>

## Threading & Mounting

M35.5 x 0.50	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>

## Regulatory Compliance

<a href="#">Exempt</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Contains SVHC(s)</a>	<b>REACH 241:</b>
Japan	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Up to 1", C-Mount Lens
- "Fast" Lenses for Increased Throughput
- 4.7mm to 75mm Focal Length

1" Format Fixed Focal Length Lenses provide high throughput and high resolution across the entire camera sensor, allowing for excellent imaging even in less-than-ideal lighting conditions. Offered in 9 focal lengths from 4.7mm to 75mm, this complete family covers many of the applications in the market today. Engineered to minimize distortion, these lenses provide a perfect image for a human operator or an automated system. 1" Format Fixed Focal Length Lenses also feature a standard C-Mount lens mount for easy integration with the most common machine vision [cameras](#) we offer. All lenses feature front filter threading to attach to your choice of [optical filter](#).