

[See all 36 Products in Family](#)

# 1.8mm Dia, 670nm DWL, 0.0mm WD, Uncoated, GRIN Lens



Stock **#64-519** [CONTACT US](#)

-

1

+

₹6,266

 Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹6,266 each                   |
| Qty 11-49      | ₹5,522 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Gradient Index Lens

Physical & Mechanical Properties

Diameter (mm):

1.80 +0.00/-0.01

Clear Aperture (%):

90.00

Length (mm):

|                                                                                              |        |
|----------------------------------------------------------------------------------------------|--------|
| 4.34                                                                                         |        |
|                                                                                              | Pitch: |
| 0.25                                                                                         |        |
| Length Tolerance (%):                                                                        |        |
| ±5                                                                                           |        |
| Optical Properties                                                                           |        |
| Effective Focal Length EFL (mm):                                                             |        |
| 1.70                                                                                         |        |
| Substrate:  |        |
| Aluminosilicate Glass Embedded with Silver Ions                                              |        |
| f/#:                                                                                         |        |
| 0.92                                                                                         |        |
| Numerical Aperture NA:                                                                       |        |
| 0.52                                                                                         |        |
| Coating:                                                                                     |        |
| Uncoated                                                                                     |        |
| Wavelength Range (nm):                                                                       |        |
| 400 - 1600                                                                                   |        |
| Focal Length Specification Wavelength (nm):                                                  |        |
| 670.00                                                                                       |        |
| Gradient Constant (mm <sup>-1</sup> ):                                                       |        |
| 0.362                                                                                        |        |
| Index of Refraction (n <sub>d</sub> ) - Center of Lens:                                      |        |
| 1.629                                                                                        |        |
| Surface Quality:                                                                             |        |
| 40-20                                                                                        |        |
| Working Distance (mm):                                                                       |        |
| 0                                                                                            |        |
| Working Distance Tolerance (mm):                                                             |        |
| ±0.02                                                                                        |        |


|                                                                                                                                                                                                         |  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| Regulatory Compliance                                                                                                                                                                                   |  |
| RoHS 2015:                                                                                                                                                                                              |  |
| Compliant                                                                                                                                                                                               |  |
| Reach 219:                                                                                                                                                                                              |  |
| Compliant                                                                                                                                                                                               |  |
| Certificate of Conformance:                                                                                                                                                                             |  |
| View                                                                                                                                                                                                    |  |
| Country of Origin:                                                                                                                                                                                      |  |
| Germany                                                                                                                                                                                                 |  |
| Imported By:                                                                                                                                                                                            |  |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 |  |

## Product Details


- Ideal for Fiber Coupling and Laser Diode Applications
- Comparable Performance to Conventional Aspherical Singlets
- Multiple Sizes and Wavelength Options
- [GRIN Lens Grippers and Table Mounts](#) Available

Gradient Index (GRIN) Rod Lenses feature plane optical surfaces and achieve focus via a continuous change of the refractive index within the lens material. By eliminating complex geometries (such as aspherical surface figures) and carefully designing the lenses for specific working distances, these microlenses are comparatively easy to handle and integrate into optical systems. Gradient Index (GRIN) Rod Lenses are designed to provide a 0.55 numerical aperture. These Rod Lenses are available for purchase in 2 working distance options: 0 and 0.23 mm.

Lenses with a 0mm working distance are ideal for the collimation of single and multi-mode optical fibers and laser diodes because the lens can be positioned and glued directly to the emission source. For focusing applications, or in instances where the lens can't be in direct contact with the emission source, all lenses are available with a small working distance as well. Each lens is available uncoated (approximately 12% reflection loss), or with a BBAR coating option for R < 0.5%.



## Technical Information



;