

[See all 7 Products in Family](#)

## 2" x 2" Positive, USAF 1951 Hi-Resolution Target



Stock #58-198 [CONTACT US](#)

⊖ 1 ⊕ ₹72,450

[ADD TO CART](#)

### Volume Pricing

Qty 1-4	₹72,450 each
Qty 5+	₹68,913 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Positive Target **Type:**

Pattern Location is Centered **Note:**

High Resolution **Options:**

No **NST Certification:**

#### Physical & Mechanical Properties

2 x 2 ±0.04	<b>Dimensions (inches):</b>
1.50 ±0.05	<b>Thickness (mm):</b>
Beveled	<b>Edges:</b>
≤0.00254	<b>Flatness (mm):</b>
<b>Optical Properties</b>	
Vacuum-Deposited Durable Chromium	<b>Coating:</b>
Float Glass	<b>Substrate:</b>
≥3.0	<b>Optical Density OD (Average):</b>
Minimum: Group 0, Element 1 Maximum: Group 9, Element 3	<b>Resolution:</b>
20-10	<b>Surface Quality:</b>


<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">Compliant</a>	<b>Reach 223:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
Switzerland	<b>Country of Origin:</b>
Edmund Optics India Private Limited	<b>Imported By:</b>

## Product Details

- Negative and Positive Patterns On Glass
- Two Sizes Available
- Each is Boxed and Includes Resolution Value Chart
- High Resolution Target Available (down to 645 lp/mm)

USAF 1951 Glass Slide Resolution Test Targets are available in either positive (chrome pattern on clear background) or negative (clear pattern on a chrome background). The positive pattern is recommended for the quality control of microscopes and magnifiers. The negative pattern is ideal for collimators and other illuminated test equipment. USAF 1951 Glass Slide Resolution Test Targets are boxed and include a resolution value chart. The targets conform to ML-S-150A

## Technical Information



Element	Group Number										For High Res only	
	-2	-1	0	1	2	3	4	5	6	7	8	9
1	0.250	0.500	1.00	2.00	4.00	8.00	16.00	32.0	64.0	128.0	256.0	512.0
2	0.280	0.561	1.12	2.24	4.49	8.98	17.95	36.0	71.8	144.0	287.0	575.0
3	0.315	0.630	1.26	2.52	5.04	10.10	20.16	40.3	80.6	161.0	323.0	645.0
4	0.353	0.707	1.41	2.83	5.66	11.30	22.62	45.3	90.5	181.0	362.0	—
5	0.397	0.793	1.59	3.17	6.35	12.70	25.39	50.8	102.0	203.0	406.0	—
6	0.445	0.891	1.78	3.56	7.13	14.30	28.50	57.0	114.0	228.0	456.0	—

Condition	Positive Test Target	Negative Test Target
Lighting Condition	Front-lit or general lighting	Back-lit or highly illuminated
Appearance of Bars	Dark bars on a bright background	Bright bars on a dark background
Application	General optical testing	High-contrast or back-lit testing

---

<b>Substrate</b>	Clear substrate with chrome patterns	Chrome-covered substrate with clear patterns
<b>Example Use Case</b>	Microscope calibration	Projection systems, back-lit displays

---