


[See all 153 Products in Family](#)

## 2.0 OD, 12.5mm Dia., NIR II Coated, Absorptive ND Filter

See More by [Hoya](#)



Anti-Reflection (AR) Coated HOYA Absorptive Neutral Density (ND) Filters

Stock **#13-230** 1 In Stock

-

1

+

₹4,282

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹4,282 each                   |
| Qty 11-25      | ₹3,737 each                   |
| Qty 26-49      | ₹3,581 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

|                               |                         |
|-------------------------------|-------------------------|
| Type:                         | Neutral Density Filter  |
| Stock No. of Uncoated Filter: | <a href="#">#48-531</a> |

Physical & Mechanical Properties

|                |  |
|----------------|--|
| Diameter (mm): |  |
|----------------|--|

|           |                             |
|-----------|-----------------------------|
| 12.50     |                             |
|           | Thickness (mm):             |
| 2.00 ±0.5 |                             |
|           | Dimensional Tolerance (mm): |
| ±0.1      |                             |
|           | Parallelism (mm):           |
| <0.02     |                             |

|                                              |  |
|----------------------------------------------|--|
| Optical Properties                           |  |
| Optical Density OD (Average):                |  |
| 2 ±0.3 @ 400-700nm (Uncoated Filter)         |  |
| Nominal Optical Density @ Center of Coating: |  |
| 1.02 @ 1200nm                                |  |
| Glass/Filter Number:                         |  |
| <a href="#">Hoya ND0.3</a>                   |  |
| Substrate: <input type="checkbox"/>          |  |
| ND Filter Glass                              |  |
| Coating:                                     |  |
| NIR II (750-1550nm)                          |  |
| Index of Refraction (n <sub>d</sub> ):       |  |
| 1.51                                         |  |
| Surface Quality:                             |  |
| 80-50                                        |  |
| Transmission (%):                            |  |
| 1.0 (average) @ 400 - 700nm                  |  |
| Blocking Wavelength Range (nm):              |  |
| 400 - 700                                    |  |
| Coating Specification:                       |  |
| R <sub>abs</sub> ≤1.5% @ 750 - 800nm         |  |
| R <sub>abs</sub> ≤1.0% @ 800 - 1550nm        |  |
| R <sub>avg</sub> ≤0.7% @ 750 - 1550nm        |  |

|            |                        |
|------------|------------------------|
|            | Wavelength Range (nm): |
| 750 - 1550 |                        |

|                                  |  |
|----------------------------------|--|
| Material Properties              |  |
| Transformation Temperature (°C): |  |
| 490                              |  |


|                                     |  |
|-------------------------------------|--|
| Regulatory Compliance               |  |
| RoHS 2015:                          |  |
| <a href="#">Compliant</a>           |  |
| Certificate of Conformance:         |  |
| <a href="#">View</a>                |  |
| Reach 250:                          |  |
| <a href="#">Compliant</a>           |  |
| Country of Origin:                  |  |
| Japan                               |  |
| Imported By:                        |  |
| Edmund Optics India Private Limited |  |

## Product Details

- Optical Densities from 0.1 to 4.0
- VIS 0°, NIR I, and NIR II Coating Options
- 12.5, 25, and 50mm Diameter Sizes
- Uncoated [HOYA](#) or [SCHOTT](#) ND Filters Also Available

Anti-Reflection (AR) Coated HOYA Absorptive Neutral Density (ND) Filters feature HOYA colored glass substrates that are AR coated on both surfaces to reduce back reflections in the visible or near-infrared (NIR) spectra. VIS 0°, NIR I, and NIR II broadband AR coatings cover the spectral ranges of 425-675nm, 600-1050nm, and 750-1550nm. These neutral density filters attenuate light via absorption and can be stacked together to achieve custom optical densities to meet application requirements. Anti-Reflection (AR) Coated HOYA Absorptive Neutral Density (ND) Filters are ideal for use in imaging and detection applications to reduce stray light, as well as in general filter stacking applications to control intensity. The standard metric diameters of 12.5, 25, and 50mm are compatible with our [TECHSPEC® C, S, and T-Mount Circular Optic Mounts](#) for benchtop applications.

## Technical Information





## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts