

[See all 28 Products in Family](#)

2.0 OD, 25mm Dia., Precision Anti-Reflection (AR) Coated Absorptive ND Filter



Precision Absorptive Neutral Density (ND) Filters

Stock #16-069 **4 In Stock**

MRP ₹11,805

Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | ₹11,805 each |
| Qty 11-25 | ₹10,694 each |
| Qty 26-49 | ₹9,635 each |
| Need More? | Request Quote |

Product Downloads

General

Neutral Density Filter **Type:**

Physical & Mechanical Properties

25.00 **Diameter (mm):**

Thickness (mm):

2.06 (nominal)

90 Clear Aperture (%):

<30 Parallelism (arcsec):

Optical Properties

Optical Density OD (Average):
2.0 ±10% @ 550nm

Glass/Filter Number:
SCHOTT NG3

Substrate:
ND Filter Glass

Coating:
BBAR (450-700nm)

Index of Refraction (n_d):
1.51

Surface Quality:
80-50

Transmission (%):
1.00

Blocking Wavelength Range (nm):
400 - 700

Transmitted Wavefront, P-V:
 $\lambda/4$

Coating Specification:
 $R_{avg} \leq 1.0\% @ 450 - 700nm @ 0^\circ$

Material Properties

Transformation Temperature ($^\circ C$):
462

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
[View](#)

REACH 241:
Compliant

Country of Origin:
United States


Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details


- $\lambda/4$ Transmitted Wavefront Distortion
- AR Coated for 450 - 700nm
- Optical Densities from 0.1 to 4.0 Available
- **Absorptive Neutral Density (ND) Filters** Also Available

Precision Anti-Reflection (AR) Coated Absorptive Neutral Density (ND) Filters feature SCHOTT NG Colored Glass substrates that are polished to achieve a transmitted wavefront distortion (TWFD) specification of $\lambda/4$. These filters are coated on both surfaces with an anti-reflection (AR) coating from 450 - 700nm, reducing back reflections and enabling filter stacking with less losses and artifacts. Precision Anti-Reflection (AR) Coated Absorptive Neutral Density (ND) Filters are available with optical densities from 0.1 to 4.0 and can be stacked together to achieve custom optical densities to meet application requirements. These neutral density filters are available in 25mm diameter or 50mm square sizes and are ideal for machine vision, imaging, or low power laser applications.


Technical Information



Precision Absorptive Neutral Density (ND) Filters



**Precision Absorptive Neutral Density (ND) Filters
Typical AR Coating Performance**



Compatible Mounts

;