

[See all 33 Products in Family](#)

20 x 20mm, 800µm Pitch, 1.7° Div., Double Cyl. Lens Array UV-VIS



Stock #72-606 **3 In Stock**

- 1 + MRP ₹99,449

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹99,449 each
Qty 11-25	₹79,846 each
Qty 26-49	₹74,587 each
Need More?	Request Quote

Product Downloads

General

Lens Array **Type:**

Physical & Mechanical Properties

20.0 x 20.0 ±0.10 **Dimensions (mm):**

11.100 **Radius R (mm):**

2.00 ±0.10 **Thickness (mm):**

Optical Properties

24.70 @ 1064nm **Effective Focal Length EFL (mm):**

Fused Silica (Corning 7980) **Substrate:** □

UV-NIR (250-700nm) **Coating:**

250 - 700 **Wavelength Range (nm):**

Coating Specification:
R_{abs} ≤1.0% from 350 - 450nm @ 0° AOI
R_{avg} ≤1.5% @ 250 - 700nm @ 0°

1.7 (Full Width) **Divergence Angle (°):**

800.00 **Pitch (µm):**

Double-Sided (with cross-oriented lenses) **Array Type:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 250:**

Switzerland **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.