

[See all 36 Products in Family](#)

## 50m x 200mm Roll of MaxiBlack Film, Low Outgassing Adhesive

See More by [Acktar](#)



Actar Light Absorbent Foil and Film Rolls



Stock #17-457 [CONTACT US](#)

- 1 + MRP ₹8,00,748

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹8,00,748 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

MXB-20x5000-3 **Model Number:**

Low Outgassing Adhesive **Type:**

20 x 5000 **Dimensions (cm):**

**Note:**  
Typical Adhesive Outgassing Performance: 0.85%  
TML, 0% VCM per ASTM E595-77/84/90

## Physical & Mechanical Properties

**Dimensions (mm):**  
200 x 50000

**Foil Thickness (µm):**  
75

**Adhesive Thickness (µm):**  
60

## Optical Properties

**Coating:**  
MaxiBlack™

**Coating Thickness (µm):**  
4 - 6

**Wavelength Range (µm):**  
0.3 - 5

## Environmental & Durability Factors

**Operating Temperature (°C):**  
-40 to +150

**Abrasion Resistance:**  
Moderate

**Humidity Resistance:**  
ML-C-48497A

## Regulatory Compliance

**RoHS 2015:**  
Compliant

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
Compliant

**Country of Origin:**  
Israel

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- 25m Large Roll Formats for Volume Applications
- MaxiBlack™, Metal Velvet™, or Spectral Black™ Coatings
- Standard, Low Outgassing, or No Adhesive Options
- [Die Cut Lables](#) and [Smaller Sheet Sizes](#) Available

Acktar Light Absorbent Foil and Film Rolls feature MaxiBlack™, Metal Velvet™, and Spectral Black™ light absorbent coatings on large 25m rolls. Acktar black coatings are used in optical applications to reduce stray light, improve signal to noise ratio, and eliminate unwanted reflections. These completely inorganic coatings have wideband performance from the UV to IR, a broad operating temperature range, high vibration stability, and low outgassing. Acktar Light Absorbent Foil and Film Rolls are ideal for volume applications in aerospace, automotive, defense, and remote sensing where large areas require blackening.

**Note:** Please contact us for longer Acktar Light Absorbent Foil and Film Rolls.

Acktar Light Absorbent Foil and Film Rolls are offered in Metal Velvet (diffusive coating on aluminum), Spectral Black (semi-specular coating on aluminum), or MaxiBlack (diffusive coating on polyimide). Metal Velvet offers superior light absorption performance while Spectral Black is more durable. MaxiBlack, in addition to being durable and flexible, is nonconductive and can be used in applications that require light absorbing materials with no electrical conductivity.

## Technical Information

Light Absorbing Coatings - Hemispherical Reflectance



