

[See all 36 Products in Family](#)

50m x 200mm Roll of MaxiBlack Film, No Adhesive

See More by [Acktar](#)



Aktar Light Absorbent Foil and Film Rolls



Stock #17-455 [CONTACT US](#)

1 MRP ₹7,44,462

Price inclusive of all taxes

[ADD TO CART](#)

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | ₹7,44,462 each |
| Need More? | Request Quote |

Product Downloads

General

MXB-20x5000-0 **Model Number:**

No Adhesive **Type:**

20 x 5000 **Dimensions (cm):**

Physical & Mechanical Properties

200 x 50000 **Dimensions (mm):**

75 **Foil Thickness (µm):**

Optical Properties

MaxiBlack™ **Coating:**

4 - 6 **Coating Thickness (µm):**

0.3 - 5 **Wavelength Range (µm):**

Environmental & Durability Factors

-250 to +290 **Operating Temperature (°C):**

Moderate **Abrasion Resistance:**

ML-C-48497A **Humidity Resistance:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

Israel **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 25m Large Roll Formats for Volume Applications
- MaxiBlack™, Metal Velvet™, or Spectral Black™ Coatings
- Standard, Low Outgassing, or No Adhesive Options
- [Die Cut Labels](#) and [Smaller Sheet Sizes](#) Available

Acktar Light Absorbent Foil and Film Rolls feature MaxiBlack™, Metal Velvet™, and Spectral Black™ light absorbent coatings on large 25m rolls. Acktar black coatings are used in optical applications to reduce stray light, improve signal to noise ratio, and eliminate unwanted reflections. These completely inorganic coatings have wideband performance from the UV to IR, a broad operating temperature range, high vibration stability, and low outgassing. Acktar Light Absorbent Foil and Film Rolls are ideal for volume applications in aerospace, automotive, defense, and remote sensing where large areas require blackening.

Note: Please contact us for longer Acktar Light Absorbent Foil and Film Rolls.

Acktar Light Absorbent Foil and Film Rolls are offered in Metal Velvet (diffusive coating on aluminum), Spectral Black (semi-specular coating on aluminum), or MaxiBlack (diffusive coating on polyimide). Metal Velvet offers superior light absorption performance while Spectral Black is more durable. MaxiBlack, in addition to being durable and flexible, is nonconductive and can be used in applications that require light absorbing materials with no electrical conductivity.

Technical Information

Light Absorbing Coatings - Hemispherical Reflectance

