


[See all 6 Products in Family](#)

200 x 260mm Sheet of Fractal Black Foil, Standard Adhesive

See More by [Acktar](#)



Stock **#75-434** NEW [CONTACT US](#)

-

1

+

₹23,229

ADD TO CART

Volume Pricing	
Qty 1+	₹23,229 each
Need More?	Request Quote

Product Downloads

General

FBC-20X26-1	Model Number:
Standard Adhesive	Type:

Physical & Mechanical Properties

200 x 260	Dimensions (mm):
100	Foil Thickness (µm):

60	Adhesive Thickness (µm):
4.00	Thickness (mm):
Optical Properties	
Fractal Black™	Coating:
Copper	Substrate: □
<5	Coating Thickness (µm):
VIS - FIR	Wavelength Range (µm):
Environmental & Durability Factors	
-50 to +150	Operating Temperature (°C):
Moderate	Abrasion Resistance:
ML-C-48497A	Humidity Resistance:
Regulatory Compliance	
View	Certificate of Conformance:
Israel	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Copper Foil Increases Thermal and Electrical Conductivity
- Consistent Performance in High Temperature Environments
- Standard, Low Outgassing, and No Adhesive Options Available

Acktar Fractal Black on Copper Foils provide thermal management and light absorption for applications where direct coating is not feasible. The addition of copper foil enhances the thermal and electrical conductivity of Fractal Black, making it ideal for applications in laser devices and platforms, passive and thermal control, IR systems, space, and vacuum. The foil is designed to be flexible, lightweight, and easily cut to size for simple application and installation on a variety of surfaces. Acktar Fractal Black on Copper Foils is available in standard, low outgassing, and no adhesive options.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).