

[See all 31 Products in Family](#)

## 200mm Articulating Arm for SCHOTT EasyLED Spotlights

See More by [SCHOTT Optical Components](#)



200mm Articulating Arm for SCHOTT EasyLED Spot Lights

Stock **#15-930** **1 In Stock**

⊖ 1 ⊕ ₹24,750

**ADD TO CART**

### Volume Pricing

Qty 1+	₹24,750 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

158.345 **Model Number:**

Accessory **Type:**

SCHOTT **Manufacturer:**

### Hardware & Interface Connectivity

**Power Supply:**  
Power Supply Required and Sold Separately.

USA: #15-907  
 Europe: #15-907  
 Japan: #15-907  
 Korea: #15-907  
 China: #15-907

## Threading & Mounting

### Mounting Threads:

2 x M6

## Regulatory Compliance

### Certificate of Conformance:

[View](#)

### Country of Origin:

Germany

### Imported By:

Edmund Optics India Private Limited

## Product Details

- Ringlight, Backlight, and Spotlight Illuminators
- Integrated Controllers for Intensity Adjustment
- Designed for Easy Integration into Microscopy Systems

SCHOTT EasyLED Series Illuminators are compact illuminators with integrated controllers that provide continuous intensity adjustment. These illuminators are available as ringlights, backlights, or spotlights, and accessories are available to integrate each type of illuminator into microscopy systems. EasyLED Ringlights offer homogenous, shadow-free illumination, while the Ringlights Plus also features controllable LED segments for enhanced contrast adjustment. EasyLED Backlights are designed to fit common microscope stand sizes from 84 to 180mm in diameter and provide uniform illumination over their large 50mm diameter active area. EasyLED Spotlights can be mounted to any microscope stand to facilitate integration into existing microscopy systems and are available with one or two adjustable spotlights. SCHOTT EasyLED Series Illuminators are an ideal replacement for conventional cold light sources using fiber optics in machine vision or microscopy applications.

## Technical Information

### System Diagram for EasyLED Series

