

[See all 30 Products in Family](#)

## 200mm Dia x 600mm Focal Length, MgF<sub>2</sub> Coated, PCX Condenser Lens



Stock #19-916 **4 In Stock**

- 1 + MRP ₹67,092

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹67,092 each
Qty 11-49	₹60,736 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Condenser Lens **Type:**

### Physical & Mechanical Properties

200.00 +0.0/-0.5 **Diameter (mm):**

21.60 **Center Thickness CT (mm):**

**Edge Thickness ET (mm):**

5.03

Clear Aperture CA (mm):

195

Bevel:

Protective as needed

### Optical Properties

Effective Focal Length EFL (mm):

600.00 @587.6nm

Back Focal Length BFL (mm):

586.00

Coating:

MgF<sub>2</sub> (400-700nm)

Coating Specification:

R<sub>avg</sub> ≤1.75% @400 - 700nm

Substrate:

N-BK7

Surface Quality:

120-80

Radius R<sub>1</sub> (mm):

310.00

f#:

3.00

Numerical Aperture NA:

0.17

Wavelength Range (nm):

400 - 700

### Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 235:

Compliant

Country of Origin:

United States

Imported By:


Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Large Sizes Available – 100 to 250mm Diameter
- Polished Surfaces for Superior Precision vs. Cast Optics
- Wavelength Range of 350-2200nm

Large PCX Condenser Lenses are condenser lenses that concentrate light into a projected beam. They are used in projectors, enlargers, spotlights, and other projection and illumination applications. Our large condensers are available in sizes not available in our standard PCX lenses and are available in a variety of focal lengths. Combine two condenser lenses of the same focal length to produce a system with half the focal length of a single lens. Large PCX Condenser Lenses are available uncoated or with a MgF<sub>2</sub> coating. These lenses feature a N-BK7 substrate and are offered in diameters ranging from 100 to 250mm.

## Technical Information



## Coating Curves

