

[See all 12 Products in Family](#)

TECHSPEC® 20mm Dia., VIS Coated, Linear Glass Polarizer (XP42)



Stock #19-649 **20+ In Stock**

⊖ 1 ⊕ ₹11,366

ADD TO CART

Volume Pricing	
Qty 1-9	₹11,366 each
Qty 10+	₹10,043 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

20.00 **Diameter (mm):**

2.00 ±0.10 **Thickness (mm):**

+0.00/-0.20 **Dimensional Tolerance (mm):**

Laminated Glass Polarizing Film

Construction:

Optical Properties

VIS AR Coated

Coating:

9000:1 @ 546nm

Extinction Ratio:

XP42 Laminated Between Glass

Substrate: □

45 @ 546nm

Transmission (%):

$R_{avg} < 0.5\%$ @ 425 - 700nm

Coating Specification:

425 - 700

Wavelength Range (nm):

>99.98 @ 546nm

Polarization Efficiency (%):

Environmental & Durability Factors

-10 to +55

Operating Temperature (°C):

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 235:

Japan

Country of Origin:

Edmund Optics India Private Limited

Imported By:

Product Details

- Uncoated and Visible AR Coated Options
- >99.98% Polarization Efficiency
- 42% Transmission for Uncoated and 45% Transmission for AR Coated Versions
- XP42 **Plastic** and **Film** Also Available

TECHSPEC® High Contrast Glass Linear Polarizers (XP42) are a high transmission, high efficiency solution that are ideal for a broad range of industrial and laboratory applications. Featuring a >99.98% polarization efficiency and an extinction ratio of 9000:1, these polarizers are constructed with an **XP42 high contrast linear polarizing film** laminated between two pieces of optical grade glass. TECHSPEC High Contrast Glass Linear Polarizers (XP42) are available uncoated or with a visible AR coating that provides increased transmission from 425 – 700nm. Typical single filter transmission with randomly polarized incident light is 42% for the uncoated options and 45% for the AR coated options.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).