

[See all 88 Products in Family](#)

20mm Dia. x 11.1mm FL, NIR I Coated, Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#15-889** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

MRP ₹7,213

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹7,213 each
Qty 11-49	₹6,357 each
Need More?	Request Quote

Product Downloads

General

Condenser Lens

Type:

Note:
[Click here](#) for more information on the ISO 10110 surface quality specification.

Physical & Mechanical Properties

Diameter (mm):

20.00 +/-0.3	
Centering (arcmin):	≤30
Clear Aperture CA (mm):	16.00
Edge Thickness ET (mm):	2.5 ±0.3
Center Thickness CT (mm):	10.90 (nominal)
Bevel:	Protective as needed
Diameter of Asphere (mm):	19.8
Shape of Back Surface:	Convex

Optical Properties

Effective Focal Length EFL (mm):	11.10 @ 587.6nm
Numerical Aperture NA:	0.89
Back Focal Length BFL (mm):	4.90
Substrate: □	Liba2000+
Focal Length Tolerance (%):	±7
Coating:	NIR I (600-1050nm)
Coating Specification:	R _{avg} ≤0.5% @ 600 - 1050nm
Surface Quality:	5/3 x 0.4; E 0.2
f#:	0.56
Abbe Number (v _d):	58.85
Index of Refraction (n _d):	1.520
Radius R ₂ (mm):	17.7
Wavelength Range (nm):	600 - 1050
Conjugate Distance:	Infinite
Focal Length Specification Wavelength (nm):	587.6

Material Properties

Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):	9.4
--	-----

Regulatory Compliance


RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 242:	Compliant
Country of Origin:	United States
Imported By:	Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000

Product Details

- Hardened for Improved Durability
- High Numerical Apertures
- Ideal for Illumination Applications

Molded Aspheric Condenser Lenses are pressed, hardened, and annealed to meet precise optical and mechanical specifications. The hardening process improves the durability of the lenses, making them less susceptible to thermal shock and scratching than traditionally polished lenses. These Molded Aspheric Condenser Lenses are ground and polished on the second surface, enhancing the overall precision of the lenses. Molded Aspheric Condenser lenses are ideal for a wide range of illumination and detection applications, including biotech instruments such as DNAsequencers and polymerase chain reaction (PCR) testing platforms.

Technical Information



Compatible Mounts