

[See all 88 Products in Family](#)

## 20mm Dia. x 16.4mm FL, NIR I Coated, Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#15-892** **4 In Stock**

[Other Coating Options](#)

1  MRP ₹7,213

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹7,213 each
Qty 11-49	₹6,357 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Condenser Lens **Type:**

**Note:**  
[Click here](#) for more information on the ISO 10110 surface quality specification.

#### Physical & Mechanical Properties

**Diameter (mm):**

20.00 +/-0.3

Centering (arcmin):  
≤25

Clear Aperture CA (mm):  
18.00

Edge Thickness ET (mm):  
1.5

Center Thickness CT (mm):  
6.40 ±0.20

Bevel:  
Protective as needed

Diameter of Asphere (mm):  
20.0

Shape of Back Surface:  
Convex

## Optical Properties

Effective Focal Length EFL (mm):  
16.40 @ 587.6nm

Numerical Aperture NA:  
0.61

Back Focal Length BFL (mm):  
12.85

Substrate:   
[Liba2000+](#)

Focal Length Tolerance (%):  
±5

Coating:  
NIR I (600-1050nm)

Coating Specification:  
R<sub>avg</sub> ≤0.5% @ 600 - 1050nm

Surface Quality:  
Molded Side: 5/3 x 0.4; E 0.2  
Polished Side: 5/3 x 0.25; E 0.2

f#:  
0.82

Abbe Number (v<sub>d</sub>):  
58.85

Index of Refraction (n<sub>d</sub>):  
1.520

Radius R<sub>2</sub> (mm):  
44.97

Wavelength Range (nm):  
600 - 1050

Conjugate Distance:  
Infinite

Focal Length Specification Wavelength (nm):  
587.6

## Material Properties

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):  
9.4

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 242:  
[Compliant](#)

Country of Origin:  
United States

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details

- Hardened for Improved Durability
- High Numerical Apertures

- Ideal for Illumination Applications

Molded Aspheric Condenser Lenses are pressed, hardened, and annealed to meet precise optical and mechanical specifications. The hardening process improves the durability of the lenses, making them less susceptible to thermal shock and scratching than traditionally polished lenses. These Molded Aspheric Condenser Lenses are ground and polished on the second surface, enhancing the overall precision of the lenses. Molded Aspheric Condenser lenses are ideal for a wide range of illumination and detection applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms.

## Technical Information



## Compatible Mounts