

TECHSPEC[®] 2.0mm Diameter, N-SF8 Ball Lens



TECHSPEC[®] N-BK7 Ball Lenses

Stock **#43-713** CLEARANCE **2 In Stock**

-

1

+

MRP ₹1,056

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,056 each
Need More?	Request Quote

Product Downloads

General	
Ball Lens	Type:
Physical & Mechanical Properties	
2.00	Diameter (mm):
±3.0	Diameter Tolerance (µm):
Optical Properties	

N-SF8	Substrate: 
Uncoated	Coating:
1.689	Index of Refraction (n _d):
0.625	Sphericity (μm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Switzerland	Country of Origin:
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Can be Used as Fiber Coupling Spheres or Collimating Lenses
- Ideal Pre-Forms for Aspheric Lenses
- Available in a Variety of Sizes
- [TECHSPEC® N-BK7 Half-Ball Lenses](#) Also Available

TECHSPEC® N-BK7 Ball Lenses are glass spheres commonly used in fiber optic applications. Ball lenses are excellent optical components for improving signal coupling between fibers, emitters, and detectors. They are also used in endoscopy, bar code scanning, ball pre-forms for aspheric lenses, and sensor applications. TECHSPEC® N-BK7 Ball Lenses are uncoated and are optimal for wavelengths 350-2200nm. If applications require a more compact design, [TECHSPEC® N-BK7 Half-Ball Lenses](#) are also available.

Compatible Mounts