

[See all 6 Products in Family](#)

**TECHSPEC® 20mm VIS, Lateral Displacement Non-Polarized Beamsplitter**



Lateral Displacement Beamsplitters

Stock **#47-189** **20+ In Stock**

⊖ 1 ⊕ MRP ₹80,712

📌 Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹80,712 each
Qty 6-25	₹64,066 each
Qty 26-99	₹59,525 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Non-Polarizing Beamsplitter **Type:**

Non-Polarizing **Type of Optics:**

**Physical & Mechanical Properties**

Clear Aperture (%):

80.00

**Construction:**

Prism

**Dimensional Tolerance (mm):**

±0.1

**Parallelism (arcmin):**

<2

**Optical Properties**

**Angle Tolerance (arcsec):**

±5

**Beam Separation (mm):**

20.00

**Coating Specification:**

R<sub>avg</sub> <0.5% @ 430 - 670nm

**Extinction Ratio:**

|T<sub>p</sub> - T<sub>s</sub>| <6%

**P-Polarization Transmission (%):**

45.00

**Reflection/Transmission Tolerance (%):**

±10

**S-Polarization Reflection (%):**

45.00

**Substrate:**

N-BK7

**Surface Flatness (P-V):**

λ/8

**Surface Quality:**

40-20

**Wavelength Range (nm):**

430 - 670

**Regulatory Compliance**

**Certificate of Conformance:**

[View](#)

**Country of Origin:**

Singapore

**Imported By:**


Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Visible and NIR Coating Options Offered
- Simplifies Benchtop Layout
- Split Incident Beam into Two Displaced Parallel Beams

TECHSPEC® Lateral Displacement Beamsplitters output two parallel beams separated by a fixed distance. The beamsplitters consist of a precision [rhomboid prism](#) cemented to a [λ/8 right angle prism](#). The high tolerance design ensures the exiting beams are parallel to within 2 arcmin. TECHSPEC® Lateral Displacement Beamsplitters' entrance and exit faces feature a multi-layer anti-reflection (AR) coating for increased efficiency. Polarizing and non-polarizing coatings are available for these beamsplitters.

## Technical Information



Size (A)	10mm	20mm
Beam Separation	10mm	20mm

