

[See all 5 Products in Family](#)

2.2 - 13.6um InAsSb Photovoltaic Infrared Detector, PVIA-4TE-13-1x1-TO8-wZnSeAR36



2.2 - 13.6um InAsSb Photovoltaic Infrared Detector, PMA-4TE-13-1x1-TO8-wZnSeAR36

Stock **#90-464** NEW **3 In Stock**

1 MRP ₹3,35,167

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹3,35,167 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

IR Photovoltaic Detector **Type:**

PMA-4TE-13-1x1-TO8-wZnSeAR36 **Model Number:**

TO-8 **Package:**

Vigo Photonics **Manufacturer:**

Physical & Mechanical Properties

7 **Weight (g):**

1.00 x 1.00 **Active Area (mm):**

Optical Properties

2200 - 13600 **Spectral Response (nm):**

36 **Acceptance Angle (°):**

Environmental & Durability Factors

-40 to +70 **Operating Temperature (°C):**

-40 to +85 **Storage Temperature (°C):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

Poland **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Mid and Long-Wave Infrared (MMR/LMR) Spectral Range
- 1 × 1mm² Active Areas with Acceptance Angles up to 90°
- TO-39 and TO-8 Package Styles with Specialized Anti-Reflection Windows

Vigo Photonics Infrared Detectors deliver high-performance mid and long-wave IR detection with exceptional sensitivity and stability across demanding applications. These HgCdTe and InAsSb detectors are available with a variety of cooling configurations, including single, dual, triple, and quad-stage thermoelectric coolers, to optimize signal-to-noise ratios. Models are offered with active areas of 1 × 1mm² and acceptance angles up to 90°, providing flexibility for system integration. Vigo Photonics Infrared Detectors feature precision packaging options such as TO-39 and TO-8 housings with specialized anti-reflection coatings for maximum throughput. These detectors combine reliability with infrared technology, making them ideal for spectroscopy, gas analysis, and defense applications.