

[See all 102 Products in Family](#)

## 24.9mm Dia. x 17mm FL, Aspheric Condenser Lens, NIR I



Stock #72-505 **12 In Stock**

[Other Coating Options](#)

- 1 + MRP ₹5,852

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹5,852 each
Qty 11-49	₹5,246 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Condenser Lens **Type:**

#### Physical & Mechanical Properties

24.90 +0.0/-0.2 **Diameter (mm):**

≤30 **Centering (arcmin):**

22.41	<b>Clear Aperture CA (mm):</b>
1.90	<b>Edge Thickness ET (mm):</b>
11.00 ±0.30	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
24.90	<b>Diameter of Asphere (mm):</b>
Plano	<b>Shape of Back Surface:</b>
<b>Optical Properties</b>	
17.00	<b>Effective Focal Length EFL (mm):</b>
0.73	<b>Numerical Aperture NA:</b>
9.80	<b>Back Focal Length BFL (mm):</b>
H-K51	<b>Substrate:</b> <input type="checkbox"/>
±5	<b>Focal Length Tolerance (%):</b>
NIR I (600-1050nm)	<b>Coating:</b>
R <sub>avg</sub> ≤0.5% @ 600 - 1050nm	<b>Coating Specification:</b>
80-50 (typical)	<b>Surface Quality:</b>
0.68	<b>f#:</b>
∞	<b>Radius R<sub>2</sub> (mm):</b>
350 - 700	<b>Wavelength Range (nm):</b>
Infinite	<b>Conjugate Distance:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
China	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

## Technical Information



