

[See all 5 Products in Family](#)

## 25/25.4mm Replacement Wheel



#88-171 with cover



Stock **#88-371** **3 In Stock**

1  MRP ₹14,125

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹14,125 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

6 **Number of Filters:**

### Regulatory Compliance

[Compliant](#) **RoHS 2015:**

Certificate of Conformance:

View

REACH 241:  
Compliant

Country of Origin:  
United States

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details

- Manual or Automated Multi-Directional Control
- Interchangeable Filter Retaining Wheels
- Lightweight Design with Multiple Mounting Options

Miniature Motorized Filter Wheels are ideal for space constrained applications that require spectral selection, such as fluorescence microscopy, color CCD photography, or photometry. These stepper motor driven, optical encoder regulated filter wheels are designed to repeatedly select absolute positions either manually using a push button or remotely through an RS-232 or USB 2.0 interface. Miniature Motorized Filter Wheels feature two aperture positions, at 12:00 and 9:00, and a digital display which shows the current filter position. The six position filter wheel accepts 25mm filters, while the twelve position filter wheel accepts 12.5mm filters. The base of the unit features six threaded mounting holes to ease system integration, including one 1/4"-20, two #8-32, one M6, and two M4

**Note:** Accessories are available to increase or decrease compatible filter size.

## Technical Information



#88-398	
Quantity	Description
1	12.5mm Filter Wheel
1	12 Position Filter Retaining Wheel
1	5V DC Converter
1	USB 2.0A to USB Micro A (6ft cable)
1	RS-232 to RS-232 (6ft cable)
1	Software Flash Drive
2	Threaded Aperture Caps
6	Threaded 1/2" Filter Retaining Rings
1	5/64" Ball Driver
1	Operating Manual

#88-171	
Quantity	Description
1	25mm Filter Wheel
1	6 Position Filter Retaining Wheel
1	5V DC Converter
1	USB 2.0A to USB Micro A (6ft cable)
1	RS-232 to RS-232 (6ft cable)
1	Software Flash Drive
2	Threaded Aperture Caps
6	Threaded 1" Filter Retaining Rings
1	5/64" Ball Driver
1	Operating Manual