

[See all 23 Products in Family](#)

TECHSPEC® 25.4 x 25.4mm EFL 90° Protected Silver 100Å Off-Axis Parabolic Mirror



Stock **#36-586** **5 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹43,282

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹43,282 each
Qty 6-10	₹38,843 each
Qty 11-25	₹37,329 each
Need More?	Request Quote

Product Downloads

General

Off-Axis Parabolic Mirror **Type:**

Physical & Mechanical Properties

25.4 **Y Offset (mm):**

Diameter (mm):

25.40 +0.00/-0.38

90 **Clear Aperture (%)**:

<100 RMS **Surface Roughness (□)**:

Optical Properties

Metal **Coating Type**:

Protected Silver (450-12000nm) **Coating**:

90 **Off-Set Angle (°)**:

450 - 12000 **Wavelength Range (nm)**:

25.40 **Effective Focal Length EFL (mm)**:

Aluminum 6061-T6 **Substrate** □:

Coating Specification:
R_{avg} ≥98% @ 2,000 - 12,000nm,
R_{avg} (typical) 96% @ 450 - 2,000nm

±1 **Focal Length Tolerance (%)**:

12.7 **Parent Focal Length PFL (mm)**:

λ4 **Surface Figure, RMS**:

80-50 **Surface Quality**:

25.40 **Radius of Curvature (mm)**:

λ2 **Reflected Wavefront, RMS**:

Threading & Mounting

[#47-111](#) **Compatible Mounting Plates**:

Regulatory Compliance

[Compliant](#) **RoHS 2015**:

[View](#) **Certificate of Conformance**:

[Compliant](#) **Reach 247**:

United States **Country of Origin**:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Protected Silver Coating for Visible and IR Application
- 100Å Surface Roughness
- 90° Offset Angle
- Aluminum and Gold Coated Off-Axis Parabolic Mirrors Also Available

TECHSPEC® Silver Off-Axis Parabolic Mirrors (OAPs) are designed to direct and focus incident collimated light at a specific offset angle with minimal scatter loss. Coated with protected silver, these OAP mirrors provide high reflectivity from the visible to the infrared (IR), making them ideal for broadband applications. These Silver OAPs provide unobstructed access to the point of focus, allowing for the creation of more compact systems. TECHSPEC® Silver Off-Axis Parabolic Mirrors (OAPs) are commonly used in instrumentation and laser systems in the visible and IR spectrum, including Schlieren, MTF, FLIR, and FTIR systems. For additional surface roughness options and

offset angles, please see our aluminum or gold coated OAPs or [contact us](#) for custom options.

Technical Information

