

254 x 356mm, 30R/70T, Plate Beamsplitter



Stock #43-363 **3 In Stock**

MRP ₹70,119

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹70,119 each
Qty 10-24	₹51,454 each
Qty 25-49	₹49,436 each
Need More?	Request Quote

Product Downloads

General

Standard Beamsplitter **Type:**

Physical & Mechanical Properties

>85 **Clear Aperture (%):**

Plate **Construction:**

±0.38 **Dimensional Tolerance (mm):**

254.0 x 356.0 **Dimensions (mm):**

Cut **Edges:**

3.00 **Thickness (mm):**

Optical Properties

Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: AR $\frac{1}{4}\lambda$ MgF₂ @ 550nm

30/70 **Reflection/Transmission Ratio (R/T):**

Float Glass **Substrate:**

4 - 6λ **Surface Flatness (P-V):**

80-50 **Surface Quality:**

400 - 700 **Wavelength Range (nm):**

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 247:
Compliant

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- Low-Cost Design
- Multiple Sizes Available
- Many Beamsplitting Ratios Available

Plate Beamsplitters are available in multiple Reflect/Transmission ratios to meet a wide variety of application needs. These beamsplitters are also offered with an anti-reflection (AR) coating on the second surface to enhance each beamsplitter's overall efficiency. This second coating aids in preventing unwanted ghost reflections. Plate Beamsplitters are a cost-efficient option to integrate into multiple applications. For custom sizes or alternate reflection/transmission ratios, please contact our [Sales Department](#).

Technical Information



30R / 70T Beamsplitter (45°)



;