

[See all 12 Products in Family](#)

25.4mm 1064nm, High Energy Polarizing Cube Beamsplitter



Laser Line High Energy Polarizing Cube Beamsplitters

Stock **#33-319** **3 In Stock**

⊖ 1 ⊕ MRP ₹1,28,130

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹1,28,130 each
Qty 11-25	₹1,03,917 each
Qty 26-99	₹93,828 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

90 **Clear Aperture (%):**

Construction:

Cube

Dimensions (mm):

25.4 x 25.4 x 25.4 +0.0/-0.3

Optical Properties

Beam Deviation (arcmin):

<3

Design Wavelength DWL (nm):

1064

Extinction Ratio:

1000:1

Reflection (%):

$R_s > 99.5\% @ 1064\text{nm}$

Substrate:

Fused Silica (Corning 7980)

Surface Flatness (P-V):

$\lambda/6$

Surface Quality:

40-20

Transmission (%):

$T_p > 97\% @ 1064\text{nm}$

Wavelength Range (nm):

1020 - 1090

Damage Threshold, By Design:

Typical: $20 \text{ J/cm}^2 @ 1064\text{nm}$ 10ns, 20Hz

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Country of Origin:

Lithuania

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Optically Contacted Design Increases Damage Threshold and Eliminates Cement Fluorescence
- Greater than 96% Transmission of P-Polarized Light
- High Extinction Ratio of Greater than 1000:1

Laser Line High Energy Polarizing Cube Beamsplitters are an easy-to-mount, high contrast alternative to [Brewster windows](#). The beamsplitters feature greater than 96% transmission of p-polarized light, along with an $\lambda/6$ surface flatness for minimal wavefront distortion. To increase the laser damage threshold and eliminate fluorescence, these polarizers are constructed by optically contacting, rather than cementing, UV Fused Silica Right Angle Prisms. Laser Line High Energy Polarizing Cube Beamsplitters are offered in a 12.7 x 12.7 x 12.7mm or 25.4 x 25.4 x 25.4mm size. The beamsplitters are available for use with a variety of common Nd:YAG laser wavelengths.

