

25.4mm Dia., $\lambda/2$ at 1030nm and $\lambda/4$ at 515nm, Dual Wavelength Waveplate



Stock #23-751

CONTACT US

-

1

+

₹30,751

ADD TO CART

Volume Pricing	
Qty 1-5	₹30,751 each
Qty 6+	₹27,948 each
Need More?	Request Quote

Product Downloads

General

Type:

Dual Wavelength Waveplate

Physical & Mechanical Properties

Clear Aperture CA (mm):

18.0

Diameter (mm):

25.40 +0/-0.2

Dimensional Tolerance (mm):

+0/-0.2

Parallelism (arcsec):		<30
Optical Properties		
Coating:		R<0.5% @ 515 & 1030nm
Design Wavelength DWL (nm):		515, 1030
Substrate: ☐		Crystalline Quartz
Retardance:		$\lambda/4$ @ 515, $\lambda/2$ @ 1030
Surface Quality:		20-10
Transmitted Wavefront, P-V:		< $\lambda/10$ @ 632.8nm
Retardance Tolerance:		$\lambda/100$ @ 20 °C
Damage Threshold, By Design: ☐		>5 J/cm ² @ 1064 nm; 10 ns; 10 Hz
Retardance Order:		Multiple order
Threading & Mounting		
Mount Thickness (mm):		6 ±0.2
Regulatory Compliance		
RoHS 2015:		Compliant
Certificate of Conformance:		View
Reach 247:		Compliant
Country of Origin:		Lithuania
Imported By:		Edmund Optics India Private Limited

Product Details

- $\lambda/4$ and $\lambda/2$ Retardance for Harmonic Separation
- Designed for Nd:YAG, Yb:YAG, or Ti:Sapphire Lasers
- Multiple Order Designs

Dual-Wavelength Quartz Waveplates are made with high-quality crystalline quartz substrates and offer $\lambda/4$ retardance at one wavelength and $\lambda/2$ retardance at a second wavelength. Featuring designed wavelengths for Nd:YAG (532 and 1064nm), Yb:YAG (515 and 1030nm), and Ti:Sapphire (400 and 800nm), these waveplates boast high laser damage threshold (LDT) and anti-reflective (AR) coatings for high powered laser applications. Dual-Wavelength Quartz Waveplates are mounted in a 25.4mm black anodized aluminum ring with an 18mm clear aperture. These waveplates are ideal for laser separation applications requiring increased conversion efficiency of dual-wavelength sources or Second-Harmonic Generation (SHG) lasers through management of polarization.