

[See all 1 Products in Family](#)

## 25.4mm Dia. 266, 355, 532, 1064nm 45°, Low Cost Laser Line Mirror



Stock #11-613 **20+ In Stock**

- 1 + MRP ₹14,630

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹14,630 each
Qty 11-49	₹12,309 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Laser Mirror **Type:**

### Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

>90 **Clear Aperture (%):**

**Back Surface:**

Commercial Polish

25.40 +0.0/-0.1 **Diameter (mm):**

5.00 ±0.25 **Thickness (mm):**

## Optical Properties

20-10 **Surface Quality:**

98 **Reflection at DWL (%):**

**Coating Specification:**  
R<sub>abs</sub> >98% @ 266, 355, 532nm, R<sub>abs</sub> >97% @ 1064nm

λ/8 **Surface Flatness (P-V):**

Dielectric **Coating Type:**

Laser Mirror (266, 355, 532, 1064nm) **Coating:**

266, 355, 532, 1064 **Design Wavelength DWL (nm):**

45 **Angle of Incidence (°):**

**Substrate:**   
Fused Silica (Corning 7980)

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

China **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Nd:YAG Harmonic Wavelengths
- >97% Reflectivity at 266, 355, 532 and 1064nm
- Excellent Cost to Performance Ratio
- [Nd:YAG Laser Line Mirrors](#) and [Low Cost Laser Line Mirrors](#) Also Available

Low Cost Nd:YAG Multi-Line Mirrors are cost-effective mirrors with excellent reflectivity at multiple Nd:YAG harmonic wavelengths. These mirrors feature fused silica substrates with >97% reflectivity at 266, 355, 532, and 1064nm. Featuring a 20 - 10 surface quality and an angle of incidence of 45°, these low-cost mirrors have an excellent cost to performance ratio in multi-line Nd:Yag applications. Low Cost Nd:YAG Multi-Line Mirrors are an ideal replacement for metallic coated mirrors in laser optical systems that require higher reflectivity.