

[See all 2 Products in Family](#)

25.4mm Dia., 3mm Thick, Uncoated, ISP Optics Sapphire Window | AL-W-25-3

See More by [ISP Optics](#)



Stock #24-543 CLEARANCE **8 In Stock**

MRP ₹18,686

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹18,686 each
Need More?	Request Quote

Product Downloads

General

AL-W-25-3 Model Number:

Protective Window Type:

Crystal Type of Window:

Physical & Mechanical Properties

21.59 Clear Aperture CA (mm):

25.40 +0.00/-0.13	Diameter (mm):
3.00 ±0.13	Thickness (mm):
<3	Parallelism (arcmin):
Protective as needed	Bevel:
85	Clear Aperture (%):
Fine Ground	Edges:
0.27	Poisson's Ratio:
435	Young's Modulus (GPa):
1,900.00	Knoop Hardness (kg/mm²):

Optical Properties

Uncoated	Coating:
Sapphire (Al ₂ O ₃)	Substrate: <input type="checkbox"/>
1.77	Index of Refraction (n_d):
60-40	Surface Quality:
72.24	Abbe Number (v_d):
0.008 for Visible Light Orthogonal to Optical Axis	Birefringence (n_o-n_e):
Random	Axis Orientation:
330 - 5500	Wavelength Range (nm):
2λ per 25.4mm	Surface Flatness (P-V):

Material Properties

3.97	Density (g/cm³):
8.8	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Latvia	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- High Corrosion Resistance and Thermal Stability
- Higher Durability than Glass Windows
- Transmission from 0.33 – 5.5μm

ISP Optics Sapphire Windows are highly durable and transmissive protective windows that are ideal for harsh environments. Sapphire is chemically inert, insoluble in water, and resistant to common acids and alkalis. Chemically, sapphire is single crystal aluminum oxide (Al₂O₃) and is useful in a transmission range from 0.33 – 5.5μm when uncoated. ISP Optics Sapphire Windows feature a Knoop Hardness of 1900 and are resistant to scratches, digs, and fractures that might otherwise weaken fused silica substrates. These windows are often used in applications with high temperatures and pressure such as viewports for vacuum or plasma chambers.