

## 25.4mm Dia. 405nm $\lambda/2$ Quartz Waveplate Zero Order



Stock #14-296 **3 In Stock**

- 1 + MRP ₹54,986

Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹54,986 each                  |
| Qty 6+         | ₹44,392 each                  |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

### General

Crystalline Waveplate **Type:**  
Air Spaced **Configuration:**

### Physical & Mechanical Properties

20.00 **Clear Aperture CA (mm):**  
**Diameter (mm):**

25.40 +0.00/-0.25

6.00 +0.00/-0.25 **Thickness (mm):**

Crystalline **Construction:**

<3 **Parallelism (arcsec):**

## Optical Properties

Laser V-Coat (405nm) **Coating:**

405 **Design Wavelength DWL (nm):**

Crystal Quartz **Substrate:**

$\lambda/2$  **Retardance:**

10-5 **Surface Quality:**

$\lambda/10$  **Transmitted Wavefront, P-V:**

$\pm\lambda/300$  **Retardance Tolerance:**

0.0001 **Temperature Coefficient ( $\lambda^\circ\text{C}$ ):**

$R_{\text{abs}} < 0.2\%$  @ 405nm **Coating Specification:**

0 **Retardance Order:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**

China **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Zero Order and Multiple Order Waveplates
- $\lambda/4$  and  $\lambda/2$  Retardance
- Mounted in Black Anodized Aluminum Frame
- **Zero Order Polymer Waveplates** Also Available

Quartz Waveplates (Retarders) are available in multiple order and zero order. These waveplates are ideal for a range of applications. Multiple order waveplates are ideal for applications where the wavelength deviates less than  $\pm 1\%$  from the design wavelength of the waveplate. For applications with a greater than  $\pm 1\%$  deviation, zero order waveplates are recommended due to their increased bandwidth and lower sensitivity to temperature change. Quartz Waveplates (Retarders) have the fast axis marked on the edge of the mount to ease system integration.

**LASER OPTICS** MADE BY EDMUND OPTICS®  **LEARN MORE**

## Technical Information

