


[See all 2 Products in Family](#)

25.4mm Dia., 4mm Thick, 3° BBAR (2000-5000nm) Coated, ISP Optics Calcium Fluoride (CaF₂) Wedged Window

See More by [ISP Optics](#)



Calcium Fluoride (CaF₂) Wedged Windows

Stock #23-850 CLEARANCE **4 In Stock**

MRP ₹32,588

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹32,588 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**

Crystal **Type of Window:**

Physical & Mechanical Properties

Clear Aperture CA (mm):

21.59	
25.40 +0.0/-0.13	Diameter (mm):
3.00 ±0.13	Thickness (mm):
Protective as needed	Bevel:
85	Clear Aperture (%):
Fine Ground	Edges:
0.26	Poisson's Ratio:
75.8	Young's Modulus (GPa):
158.30	Knoop Hardness (kg/mm²):

Optical Properties

BBAR (2000-5000nm)	Coating:
Calcium Fluoride (CaF₂)	Substrate: <input type="checkbox"/>
1.495	Index of Refraction (n_d):
60-40	Surface Quality:
94.99	Abbe Number (v_d):
Random	Axis Orientation:
Coating Specification: R _{avg} <1.5% @ 2000-5000nm R _{abs} <3.0% @ 2000-5000nm R _{avg} <1.75% @ 2000-4000nm	
2000 - 5000	Wavelength Range (nm):
2λ @ 633nm	Surface Flatness (P-V):
3° ±0.25	Wedge Angle (°):

Material Properties

3.18	Density (g/cm³):
18.85	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
United States	Country of Origin:
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- 30 Arcmin Wedge
- Low Absorption, High Transmission
- Ideal for Harsh Environments
- [Precision Flat Calcium Fluoride Windows](#) Also Available

ISP Optics Calcium Fluoride (CaF₂) Wedged Windows feature a 30 arcmin wedge to eliminate fringe patterns from etalon effects and to prevent cavity feedback. Calcium fluoride's combination of low absorption and high damage threshold make these windows a popular choice for free-space lasers. Its low refractive index allows it to be used without an anti-reflective coating. ISP Optics Calcium Fluoride (CaF₂) Wedged Windows feature low water solubility and offer superior hardness compared to other fluoride-based substrates, making them suitable for laser applications in harsh environments. Calcium Fluoride (CaF₂) Wedged Windows provide laser output protection from environmental effects and are ideal for beam sampling applications.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools