

[See all 44 Products in Family](#)

TECHSPEC® 25.4mm Dia., 532 & 1064nm T, 266nm R 45° Thin Harmonic Separator



TECHSPEC Nd:YAG Harmonic Separators

Stock **#29-039** **9 In Stock**

1 MRP ₹37,064

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹37,064 each
Qty 6-24	₹33,347 each
Qty 25-49	₹29,630 each
Need More?	Request Quote

Product Downloads

General

Laser Window Substrate **Type:**

Physical & Mechanical Properties

90 **Clear Aperture (%):**

Construction:

Dichroic

25.40 +0.00/-0.10 **Diameter (mm):**

<3 **Parallelism (arcmin):**

3.18 ± 0.20 **Thickness (mm):**

Optical Properties

45 **Angle of Incidence (°):**

Coating Specification:
Surface 1: R_{abs}: >95% @ 266nm, T_{abs}: >98% @ 532nm, T_{abs}: >98% @ 1064nm
Surface 2: R_{abs}: <1.0% @ 532nm, R_{abs}: <1.0% @ 1064nm

266 **Reflection Wavelength (nm):**

Substrate:
Fused Silica (Coming 7980)

M10 **Surface Flatness (P-V):**

10-5 **Surface Quality:**

532, 1064 **Transmission Wavelength (nm):**

Damage Threshold, By Design:
Surface 1:
1 J/cm² @ 266nm, 20ns, 20Hz
5 J/cm² @ 532nm, 20ns, 20Hz
7.5 J/cm² @ 1064nm, 20ns, 20Hz
Surface 2:
10 J/cm² @ 20ns, 20Hz @ 532nm
15 J/cm² @ 20ns, 20Hz @ 1064nm

Regulatory Compliance

Certificate of Conformance:
[View](#)

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- M10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

Note: The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.