

[See all 7 Products in Family](#)

TECHSPEC® 25.4mm Dia., 680 - 1020nm, 70R:30T, Ultrafast Beamsplitter



TECHSPEC® Ultrafast Beamsplitters

Stock #13-832 **5 In Stock**

⊖ 1 ⊕ MRP ₹28,956

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹28,956 each
Qty 5-9	₹25,424 each
Qty 10-19	₹22,701 each
Need More?	Request Quote

Product Downloads

General

Ultrafast Non-Polarizing Beamsplitter **Type:**

Physical & Mechanical Properties

3.00 ±0.10 **Thickness (mm):**

Diameter (mm):

25.40 +0.00/-0.10

80 **Clear Aperture (%):**

<10 **Parallelism (arcsec):**

Optical Properties

Fused Silica (Coming 7980) **Substrate:**

10-5 **Surface Quality:**

45 **Angle of Incidence (°):**

680 - 1020 **Wavelength Range (nm):**

70/30 **Reflection/Transmission Ratio (R/T):**

Coating Specification:
Surface 1:
R_{avg} = 70±3% @ 680 - 1020nm
R_p = 56±3% @ 680 - 1020nm
R_s = 85±3% @ 680 - 1020nm
Surface 2:
R_s <2% @ 650 - 1100nm
R_p <1.5% @ 650 - 1100nm

GDD Specification:
Transmission: ±15 fs² @ 700 - 1080nm
Reflectivity: ±20 fs² @ 700 - 1080nm

Transmitted Wavefront Distortion:
λ/8 @ 632.8nm

Reflected Wavefront Distortion:
<λ/6 @ 632.8nm

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Lithuania **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000


Product Details

- Designs for Ti:sapphire and Yb:doped Fiber Lasers
- 90:10, 70:30, and 50:50 (R:T) Split Ratios
- Controlled Reflection and Transmission GDD

TECHSPEC® Ultrafast Beamsplitters are designed for use with femtosecond pulsed Ti:sapphire and Yb:doped fiber lasers. Their front surface features a 90:10, 70:30, or 50:50 (R:T) non-polarizing beamsplitter coating while their back surface features an anti-reflective coating to minimize losses due to reflection. Each coating has controlled dispersion to allow for predictable group delay dispersion (GDD) of the transmitted or reflected pulses. TECHSPEC Ultrafast Beamsplitters are available in standard imperial sizes for easy integration into optical systems. Please [contact us](#) if your application requires an Ultrafast Beamsplitter with a custom size or coating specifications.

Note: The arrow on the edge of these optics points towards the beamsplitter coating.

Technical Information



Compatible Mounts

