

[See all 18 Products in Family](#)

**TECHSPEC® 25.4mm Dia., 6.35mm Thick, Fused Silica Uncoated Laser Window Substrate**



TECHSPEC® Uncoated Laser Window Substrates

Stock **#37-689** **20+ In Stock**

1 MRP ₹16,546

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹16,546 each
Qty 6-25	₹14,831 each
Qty 26-49	₹13,217 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Window Substrate **Type:**

Glass **Type of Window:**

**Physical & Mechanical Properties**

**Thickness (mm):**

6.35 ±0.20	
22.86	<b>Clear Aperture CA (mm):</b>
25.40 +0.00/-0.10	<b>Diameter (mm):</b>
90	<b>Clear Aperture (%):</b>
<3	<b>Parallelism (arcmin):</b>
Protective as needed	<b>Bevel:</b>
Fine Ground	<b>Edges:</b>

## Optical Properties

Fused Silica (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>
1.458	<b>Index of Refraction (n<sub>d</sub>):</b>
10-5	<b>Surface Quality:</b>
Uncoated	<b>Coating:</b>
67.8	<b>Abbe Number (v<sub>d</sub>):</b>
200 - 2200	<b>Wavelength Range (nm):</b>
λ/10	<b>Surface Flatness (P-V):</b>

## Material Properties

7980 0F	<b>Fused Silica Grade:</b>
---------	----------------------------

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Up to 10-5 Surface Quality and λ/10 Surface Flatness Available
- Fused Silica or N-BK7 Material
- Standard Imperial Sizes for Drop-in Replacement Solutions
- [Laser Line Coated Versions](#) Available
- [Mirror Substrates](#) Also Available

TECHSPEC® Uncoated Laser Window Substrates are laser quality window substrates designed to be used in demanding laser applications. These laser window substrates are available, manufactured from fused silica for high power laser applications that require excellent thermal stability or from N-BK7 for more cost sensitive laser applications. Both the fused silica and N-BK7 laser window substrates feature precision grade λ/10 surface flatness and 10-5 surface quality, ensuring minimal disturbance to transmitted beams. TECHSPEC® Uncoated Laser Window Substrates are available in standard imperial sizes from 12.7 to 50.8mm in diameter for the convenience of drop-in replacement into existing laser systems. Custom dimensional and coating options are available, please contact us for custom inquiries.

## Compatible Mounts

