

[See all 5 Products in Family](#)

25.4mm Dia x 100mm FL, Uncoated Meniscus Lens



Stock **#72-430** **3 In Stock**

1 ₹1,946

ADD TO CART

Volume Pricing

Qty 1-9	₹1,946 each
Qty 10-24	₹1,752 each
Qty 25-49	₹1,557 each
Need More?	Request Quote

Product Downloads

General

Meniscus Lens **Type:**

Physical & Mechanical Properties

25.40 +0.00/-0.10 **Diameter (mm):**

3.60 ±0.10 **Center Thickness CT (mm):**

Centering (arcmin):

<3

Clear Aperture CA (mm):

22.86

Edge Thickness ET (mm):

1.89

Optical Properties

Effective Focal Length EFL (mm):

100.00 @587.6nm

Substrate:

N-BK7

f#:

3.94

Numerical Aperture NA:

0.13

Coating:

Uncoated

Back Focal Length BFL (mm):

95.72 @587.6nm

Design Wavelength DWL (nm):

587.6

Radius R₁ (mm):

28.67

Radius R₂ (mm):

61.628

Surface Quality:

40-20

Power (P-V) @ 632.8nm:

3 Rings

Irregularity (P-V) @ 632.8nm:

0.5 Rings

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited

Product Details

- Positive Meniscus Lens Designs
- Minimize Spherical Aberration and Reduce Spot Sizes
- 350 – 2,200nm Wavelength Range

Positive Meniscus Lenses are convex-concave lenses manufactured from N-BK7 optical glass and are designed to minimize spherical aberration and reduce spot sizes in focusing applications. When used to focus a collimated beam, the lenses should be oriented with the convex surface towards to light source to minimize spherical aberration. Combining a positive meniscus lens with another lens in a multi-element optical design will allow for a shortening of the focal length and an increase in the numerical aperture (NA) of a system without introducing significant spherical aberrations. Positive Meniscus Lenses are available with focal lengths ranging from 100 to 300mm in 25.4mm diameters sizes. allowing for easy integration into benchtop systems.