


[See all 4 Products in Family](#)

# 25.4mm Dia. x 150mm FL, 3-5µm BBAR Coated, ISP Optics Silicon (Si) PCX Lens | HDAR35-SI-PX-25-150

See More by [ISP Optics](#)



Stock #24-895 CLEARANCE 2 In Stock

MRP ₹24,819

! Price inclusive of all taxes

**ADD TO CART**

#### Volume Pricing

Qty 1+	₹24,819 each
Need More?	<a href="#">Request Quote</a>

#### Product Downloads

#### General

Type:  
 Plano-Convex Lens

Model Number:  
 HDAR35-SI-PX-25-150

#### Physical & Mechanical Properties

Diameter (mm):  
 25.40 +0.00/-0.13

<3	<b>Centering (arcmin):</b>
2.20 ±0.20	<b>Center Thickness CT (mm):</b>
2.00	<b>Edge Thickness ET (mm):</b>
22.86	<b>Clear Aperture CA (mm):</b>
Protective as needed	<b>Bevel:</b>

## Optical Properties

150.00 @4µm	<b>Effective Focal Length EFL (mm):</b>
BBAR (3000-5000nm)	<b>Coating:</b>
R <sub>avg</sub> <0.5% @3 - 5µm R <sub>abs</sub> <1.5% @3 - 5µm	<b>Coating Specification:</b>
Silicon (Si)	<b>Substrate:</b> <input type="checkbox"/>
80-50	<b>Surface Quality:</b>
1λ	<b>Irregularity (P-V) @ 632.8nm:</b>
±2	<b>Focal Length Tolerance (%):</b>
363.54	<b>Radius R<sub>1</sub> (mm):</b>
5.91	<b>f#:</b>
0.08	<b>Numerical Aperture NA:</b>
3000 - 5000	<b>Wavelength Range (nm):</b>

## Regulatory Compliance

Compliant	<b>RoHS 2015:</b>
View	<b>Certificate of Conformance:</b>
Compliant	<b>Reach 240:</b>
Latvia	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- High-Durability Anti-Reflection (HDAR) Coated for 3 - 5µm
- Ideal for Weight Sensitive Applications
- Available Focal Lengths from 25.4 – 500mm

ISP Optics Silicon (Si) Plano-Convex (PCX) Lenses feature a High Durability Anti-Reflection (HDAR) coating for increased transmission in the 3 - 5µm range. Silicon features a Knoop Hardness of 1150 making it harder and less brittle than Germanium. In addition, the HDAR coating increases the durability of the substrate, enabling use in harsh environments. ISP Optics Silicon (Si) Plano-Convex (PCX) Lenses also feature a low density of 2.329g/cm<sup>3</sup>, making them ideal for weight-sensitive IR applications such as Near-Infrared (NIR) imaging and infrared spectroscopy.