

[See all 5 Products in Family](#)

## 25.4mm Dia x 150mm FL, Uncoated Meniscus Lens



Stock #72-432 **20+ In Stock**

MRP ₹2,825

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹2,825 each
Qty 10-24	₹2,548 each
Qty 25-49	₹2,270 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Meniscus Lens **Type:**

#### Physical & Mechanical Properties

25.40 +0.00/-0.10 **Diameter (mm):**

3.10 ±0.10 **Center Thickness CT (mm):**

<3	<b>Centering (arcmin):</b>
22.86	<b>Clear Aperture CA (mm):</b>
2.00	<b>Edge Thickness ET (mm):</b>
<b>Optical Properties</b>	
150.00 @ 587.6nm	<b>Effective Focal Length EFL (mm):</b>
<a href="#">N-BK7</a>	<b>Substrate:</b> <input type="checkbox"/>
5.91	<b>f#:</b>
0.08	<b>Numerical Aperture NA:</b>
Uncoated	<b>Coating:</b>
146.34 @ 587.6nm	<b>Back Focal Length BFL (mm):</b>
587.6	<b>Design Wavelength DWL (nm):</b>
43.36	<b>Radius R<sub>1</sub> (mm):</b>
95.998	<b>Radius R<sub>2</sub> (mm):</b>
40-20	<b>Surface Quality:</b>
3 Rings	<b>Power (P-V) @ 632.8nm:</b>
0.5 Rings	<b>Irregularity (P-V) @ 632.8nm:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
China	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Positive Meniscus Lens Designs
- Minimize Spherical Aberration and Reduce Spot Sizes
- 350 – 2,200nm Wavelength Range

Positive Meniscus Lenses are convex-concave lenses manufactured from N-BK7 optical glass and are designed to minimize spherical aberration and reduce spot sizes in focusing applications. When used to focus a collimated beam, the lenses should be oriented with the convex surface towards to light source to minimize spherical aberration. Combining a positive meniscus lens with another lens in a multi-element optical design will allow for a shortening of the focal length and an increase in the numerical aperture (NA) of a system without introducing significant spherical aberrations. Positive Meniscus Lenses are available with focal lengths ranging from 100 to 300mm in 25.4mm diameters sizes. allowing for easy integration into benchtop systems.