

[See all 4 Products in Family](#)

25.4mm Dia. x 25.4mm FL, 3 - 5µm BBAR Coated, ISP Optics Silicon (Si) Aspheric Lens | HDAR35-ASPH-SI-25-25

See More by [ISP Optics](#)



Stock #24-885

CLEARANCE

CONTACT US

-

1

+

₹38,189

ADD TO CART

Volume Pricing	
Qty 1+	₹38,189 each
Need More?	Request Quote

Product Downloads

General	
HDAR35-ASPH-SI-25-25	Model Number:
Physical & Mechanical Properties	
25.40 +0.00/-0.13	Diameter (mm):
<20	Centering, ETD (µm):

22.86	Clear Aperture CA (mm):
1.73	Edge Thickness ET (mm):
3.00 ±0.20	Center Thickness CT (mm):
Protective as needed	Bevel:
Concave	Shape of Back Surface:
<100 Ra	Surface Roughness (□):

Optical Properties	
25.40	Effective Focal Length EFL (mm):
0.50	Numerical Aperture NA:
23.15	Back Focal Length BFL (mm):
Silicon (Si)	Substrate: □
BBAR (3000-5000nm)	Coating:
R _{avg} <0.5% @ 3 - 5µm R _{abs} <1.5% @ 3 - 5µm	Coating Specification:
60-40	Surface Quality:
1.00	f/#:
3000 - 5000	Wavelength Range (nm):
Infinite	Conjugate Distance:
λ/4	Irregularity (P-V) @ 632.8nm:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Latvia	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Transmission from 1.2 - 7µm
- Diffraction-Limited Performance
- Available Uncoated or HDAR Coated for 3 - 5µm

ISP Optics Silicon (Si) Aspheric Lenses provide diffraction-limited performance for weight-sensitive, Mid-Wave Infrared (MWIR) applications. Available uncoated for applications in the 1.2 - 7µm range or with a high durability anti-reflection (HDAR) coating in the 3 - 5µm range, these lenses are ideal for harsh environment or black body radiation applications. Silicon features a Knoop Hardness of 1150 making it harder and less brittle than Germanium. ISP Optics Silicon (Si) Aspheric Lenses feature a low density of 2.329g/cm³, making them lightweight alternatives to Germanium and Zinc Selenide.