

[See all 6 Products in Family](#)

TECHSPEC®

25.4mm Dia x 50.8mm FL, 1064nm V-Coat, High Precision Laser Grade Aspheric Lens



High Precision Laser Grade Aspheric Lenses

Stock **#39-560** **5 In Stock**

[Other Coating Options](#)

− 1 + MRP ₹92,819

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹92,819 each
Qty 6-10	₹83,739 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Strehl Ratio is >0.8 by design and tested **Note:**

Physical & Mechanical Properties

Diameter (mm):

25.40 +0.00/-0.05

Centering (arcmin):
<1

Clear Aperture CA (mm):
21.40

Edge Thickness ET (mm):
4.70

Center Thickness CT (mm):
8.40

Bevel:
Protective as needed

Shape of Back Surface:
Plano

Optical Properties

Effective Focal Length EFL (mm):
50.80 @ 1064nm

Numerical Aperture NA:
0.25

Back Focal Length BFL (mm):
45.03

Substrate:
[Fused Silica](#) (Corning 7980)

Aspheric Design Wavelength (nm):
1064

Asphere Figure Error, RMS @ 632.8nm:
λ/40

Coating:
Laser V-Coat (1064nm)

Coating Specification:
R_{abs} <0.25% @ 1064nm

Surface Quality:
10-5

f#:
2

Abbe Number (v_d):
67.8

Design Wavelength DWL (nm):
1064

Index of Refraction (n_d):
1.458

Spot Size (μm):
See Technical Information Tab

Conjugate Distance:
Infinite

Focal Length Specification Wavelength (nm):
1064

Damage Threshold, By Design:
15 J/cm² @ 1064nm, 20ns, 20Hz

Power (diopters):
19.69

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
0.52

Strehl Ratio:
>0.8, tested

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
Singapore

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here

to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Substrate Shape and Coating Optimized for Nd:YAG Laser Wavelengths
- High Precision Aspheric Surface
- Strehl Ratio > 0.8

TECHSPEC® High Precision Laser Grade Aspheric Lenses are polished through precision magnetorheological finishing (MRF), providing them with an ultra-smooth aspheric surface with an aspheric surface tolerance of $\lambda/40$ RMS. The aberration free aspheric surfaces produced through this super-polishing process result in these aspheric lenses having diffraction-limited performance at their design wavelengths. A high-performance Laser Line V-Coat minimizes reflection when these aspheric lenses are used at their Nd:YAG wavelengths. TECHSPEC High Precision Laser Grade Aspheric Lenses feature substrates designed and shaped at their laser wavelength to optimize the entire lens design, not just the anti-reflection coating, for the laser wavelength. Standard imperial sizes of these laser grade aspheres with $f/2$ designs, made from fused silica, are available.

Technical Information



Compatible Mounts