

[See all 16 Products in Family](#)

25.4mm Diameter Unmounted, Linear Glass Polarizing Filter



Stock #54-926 [CONTACT US](#)

- 1 + MRP ₹4,818

i Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-5	₹4,818 each
Qty 6-25	₹3,703 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

25.40 **Diameter (mm):**

2.00 ±0.2 **Thickness (mm):**

Parallelism (arcmin):

<3

Dimensional Tolerance (mm):

+0.0/-0.2

Bevel:

Protective as needed

Construction:

Dichroic Polarizing Film on Glass

Edges:

Cut

Optical Properties

Extinction Ratio:

100:1

Substrate: □

Polymer Film on [B270](#)

Surface Quality:

80-50

Transmission (%):

Single: ~30

Wavelength Range (nm):

400 - 700

Surface Flatness (P-V):

4 - 6λ

Polarization Efficiency (%):

95

Environmental & Durability Factors

Operating Temperature (°C):

-15 to +70

Regulatory Compliance

RoHS 2015:

[Compliant](#)

REACH 201:

[Compliant](#)

Certificate of Conformance:

[View](#)

Country of Origin:

Japan

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- 95% Polarization Efficiency
- 30% Typical Single Transmission of Unpolarized Light from 400 - 700nm
- 0.15% Average Crossed Transmission from 400 - 700nm
- Also Available [Mounted](#)

Linear Glass Polarizing Filters feature 95% polarization efficiency with a typical single filter transmission of 30%. The filters have a 0.15% average crossed transmission from 400-700nm. These sandwich-design polarizing filters are constructed of dichroic polarizing film on glass. Linear Glass Polarizing Filters are ideal for OEM applications, prototyping, and laboratory projects. These lightweight plastic filters are also available [mounted](#).

Technical Information

Transmission for Single Glass Polarizer

